



Inch table

Dimensions in: inches - millimeters

1		2						
d ₁	d ₂ Thread			d ₃	h ₁	h ₂ ≈	t	
1.97 50	5/16 x 18*			3/8 x 16*	1.46 37	2.52 64	0.79 20	1.02 26

Metric table

Dimensions in: millimeters - inches

1		2							
d ₁	d ₂ Thread			d ₃	d ₄	h ₁	h ₂ ≈	t	
						GN 675	GN 675.1		
43 1.69	M 6*	M 8	M 10	32.5 1.28	20 0.79	55 2.17	53.5 2.11	17.5 0.69	18 0.71
50 1.97	M 8	M 10	M 12	37 1.46	25 0.98	64 2.52	60 2.36	20 0.79	26 1.02

* Only available for EN 675

Specification

- Body
Plastic
Technopolymer (Polypropylene PP)
- Softline coating
 - Elastomer (TPE) 70 Shore A
 - Chemically bonded with the plastic core
 - FDA compliant plastic granulate
 - Temperature resistant up to 176 °F (80 °C)
 - Black, matte finish
- Tapped insert
Brass
- Color of the cover cap (EN 675.1)
 - DTR
 - DOR
 - DGR
 - DGB
 - DBL
 - DRT
 - DGN
- RoHS compliant

Information

The Softline coating makes the EN 675 and EN 675.1 ball handles particularly ergonomic and easy to grip. The **soft, slip-proof** contact area improves the grip in oily, hot / humid (hand perspiration), dry ambient conditions, and in low (below freezing) temperatures.

The ball handles are suitable for use both as operating elements and for clamping. The “hard“ plastic core guarantees the perfect anchoring of the tapped insert even under heavier clamping or torquing loads.

The transparent cover cap (DTR) of EN 675.1 allows symbols to be placed underneath. Positioning and control symbols are to be ordered separately.

Resistant to solvents, oils, grease and other chemical agents (avoid alcohol).

Accessory

- Positioning and control symbols EN 517.1
→ www.jwwinco.com

How to order (Inch, without cover cap)	
1 Ball diameter d ₁	EN 675-50-5/16X18
2 Thread d ₂	

How to order (Metric, with cover cap)	
1 Ball diameter d ₁	EN 675.1-43-M8-DBL
2 Thread d ₂	
3 Color of the cover cap	