



Metric



elesa
Original design ERB.



Metric table



Dimensions in: millimeters / inches

l ₁	b ₁	b ₂	b ₃	b ₄	h ₁	h ₂	l ₂	l ₃	s
130	59	31	41	48	29.5	3	100	124	1 ... 5
5.12	2.32	1.22	1.61	1.89	1.16	0.12	3.94	4.88	

Specification



Handle

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature
-22 °F to +212 °F (-30 °C to +100 °C)
- Black-gray, RAL 7021, matte finish
- White, RAL 9002, matte finish

- SG
- WS

Self-tapping screws ISO 7049

Steel, zinc plated ST 3.5-20

RoHS

Gripping trays EN 739 are designed for use on opening and closing sliding doors.

For mounting, the front body is first inserted into the opening of the housing and then the rear body is pushed up from behind to the housing wall. Finally, both parts are screwed together.

see also...

	Page
EN 739.1 Gripping Trays (Screw-In Type)	QVX

Technical Information

Product Family Ergostyle®	QVX
Strength Values	QVX
Plastic Characteristics	QVX

How to order

EN 739-130-SG

1 Length l₁

2 Color

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

