




Metric table

1	2	3	Dimensions in: millimeters / inches												
d ₁	d ₂	l ₁				d ₃	d ₄	d ₅	d ₆ +0.05	h ₁	h ₂	l ₂	l ₃	l ₄ ≈	
34 1.34	M 6	15 0.59	20 0.79	25 0.98	30 1.18	16 0.63	4 0.16	3.5 0.14	4.5 0.177	21 0.83	10.5 0.41	1 0.04	1.3 0.05	5.1 0.20	
42 1.65	M 8	20 0.79	25 0.98	30 1.18	40 1.57	19 0.75	6 0.24	5 0.20	6.1 0.240	26 1.02	13 0.51	1.5 0.06	1.6 0.06	6.2 0.24	
53 2.09	M 10	25 0.98	30 1.18	40 1.57	50 1.97	24 0.94	8 0.31	6.5 0.26	7.8 0.307	32 1.26	16 0.63	2 0.08	1.9 0.07	7.3 0.29	

Specification

Knob	
Plastic, Polyamide (PA)	
• Glass fiber reinforced	
• Operating temperature	
-22 °F to +266 °F (-30 °C to +130 °C)	
• Black, matte finish	
Threaded stud	
Stainless steel AISI 304	
Cover cap	
Plastic, Polyamide (PA)	
Light gray, matte finish	
RoHS	
Accessory	Page
GN 631 Thrust Pads (Plastic)	QVX
GN 631.2 Thrust Pads (NBR)	QVX
GN 631.5 Thrust Pads (Stainless Steel)	QVX

Hollow knurled knobs GN 7336.5, type MS / KU with brass or plastic tip, are used when pressure dents or damage to the clamping surface must be avoided.

The ZK type features a spherical tip whose Ø d₆ is smaller than the core Ø of the thread. This version is suitable for holding GN 631, GN 631.2 GN 631.5 thrust pads, which need to be ordered separately.

These knobs have an attractive design with the advantage of a closed shape (no recess on the underside).

see also...	Page
GN 6336.10 Star Knobs (with Brass / Plastic Tip)	QVX
GN 6336.12 Star Knobs (with Toggle Thrust Pad)	QVX
GN 421.10 Hollow Knurled Screws (with Brass / Plastic Tip)	QVX
GN 421.12 Hollow Knurled Screws (with Toggle Thrust Pad)	QVX

Technical Information

Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order		1	Handle diameter d ₁
		2	Thread d ₂
		3	Length l ₁
		4	Type
GN 7336.5-42-M8-25-MS			