

- 2 Identification no.**
- 1 Without vent hole
 - 2 With vent hole

Metric table


Dimensions in: millimeters - inches

1				3						
d ₁		EN 745.2		d ₂	d ₃	e ≈	l ₁	l ₂	s	
Pipe thread	Fine thread	Pipe thread	Vent hole							
G 1/8	M 10 x 1.5	M 12 x 1.5	-	-	2 0.08	15 0.59	22 0.87	9 0.35	16 0.63	19 0.75
G 1/4	M 14 x 1.5	-	-	G 1/4	2 0.08	15 0.59	22 0.87	9 0.35	17 0.67	19 0.75
G 3/8	M 16 x 1.5	-	-	G 3/8	2 0.08	17.5 0.69	25.5 1.00	9 0.35	18 0.71	22 0.87
G 1/2	M 18 x 1.5	M 20 x 1.5	-	G 1/2	2 0.08	21 0.83	32 1.26	11 0.43	20 0.79	27 1.06
G 3/4	M 22 x 1.5	M 25 x 1.5	M 26 x 1.5	G 3/4	2 0.08	25 0.98	37 1.46	12 0.47	22 0.87	32 1.26
G 1	M 35 x 1.5	-	-	G 1	2 0.08	31 1.22	44 1.73	13 0.51	23 0.91	38 1.50
G 1 1/4	M 40 x 1.5	-	-	G 1 1/4	2 0.08	38 1.50	53.5 2.11	14 0.55	26 1.02	46 1.81
G 1 1/2	-	-	-	G 1 1/2	2 0.08	46 1.81	63.5 2.50	15 0.59	28 1.10	55 2.17

Specification

- Body
Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Black, matte finish
- Temperature resistant up to 212 °F (100 °C)
- Seal / O-ring
Rubber NBR (Perbunan®)
- *Elastomer Characteristics* → page 2135
- *Plastic Characteristics* → page 2135
- **RoHS compliant**

Accessory



Information

For these EN 745 and EN 745.2 threaded plugs, self-adhesive, matte anodized label disks (0.3 mm thick) with graphic symbols are available in the sizes d₃ = 15 to 31 mm.

see also...

- *Fluid Drain Plugs EN 740 (Red, with Drain Symbol)* → page 1670
- *Fluid Fill Plugs EN 747 (with Fill Symbol)* → page 1672
- *Fill / Drain Plugs GN 741 / GN 742 (Aluminum)* → page 1674

How to order (With flat seal)	1 Pipe thread d ₁ (Fine thread d ₁)
EN 745-G3/4-1	2 Identification no.
How to order (With O-ring)	1 Pipe thread d ₁
EN 745.2-G1/2-1	2 Identification no.
How to order (Aluminum disks)	3 Diameter d ₃
EN 740.1-25	