



ELESA Original design TPC.

**3 Type**

- A Without dipstick
- B With dipstick

**4 Identification no.**

- 1 Without vent hole
- 2 With vent hole

**Metric table**

Dimensions in: millimeters - inches

<b>1</b> d <sub>1</sub>	<b>2</b> d <sub>2</sub> +0.2	d <sub>3</sub> Vent hole	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub>	l <sub>5</sub>
30 1.18	20 0.79	2 0.08	14 0.55	29 1.14	6.5 0.26	10.5 0.41	188 7.40
35 1.38	26 1.02	2 0.08	14 0.55	29 1.14	6.5 0.26	10.5 0.41	188 7.40

**Specification**

- Housing  
Plastic  
Technopolymer (Polypropylene PP)  
- Black, matte finish  
- Temperature resistant up to 212 °F (100 °C)
- O-ring  
NBR rubber (Perbunan®)
- Dipstick  
Steel, black phosphated finish
- RoHS compliant

**Information**

EN 748 fluid fill plugs do not require a thread. They are push-fit types and require that the minimum wall thickness of the tank must be 6.5 mm (l<sub>3</sub>).  
The dipstick has two flat sides on which the MIN-MAX fluid levels can easily be marked (see GN 109).

**On request**

- Dipsticks with special lengths or marking lines

<p>How to order</p> <p><b>EN 748-30-20-B-1</b></p>	<b>1</b>	Outside diameter d <sub>1</sub>
	<b>2</b>	Bore diameter d <sub>2</sub>
	<b>3</b>	Type
	<b>4</b>	Identification no.