



Metric



SS Stainless Steel

Metric table

2

Dimensions in: millimeters / inches

d_1	d_2	d_3	$l_1 \approx$	l_2	l_3	$l_4 \approx$	l_5	l_6
16 0.63	M 5	16 0.63	58 2.28	15 0.59	5 0.20	52.5 2.07	9.5 0.37	5 0.20
18 0.71	M 5	16 0.63	72.5 2.85	15 0.59	5 0.20	67 2.64	9.5 0.37	5 0.20
22 0.87	M 6	20 0.79	80.5 3.17	19.5 0.77	6 0.24	74 2.91	10.5 0.41	7 0.28
24 0.94	M 6	20 0.79	95.5 3.76	19.5 0.77	6 0.24	89 3.50	10.5 0.41	7 0.28
25 0.98	M 6	20 0.79	105.5 4.15	19.5 0.77	6 0.24	98.5 3.88	10.5 0.41	7 0.28

Specification

1

Handle

- Plastic, Polyamide (PA)
- Operating temperature up to 194 °F (90 °C)
- Black, matte finish
- Revolving

KT

GN 798.3

Retractable mechanism

Steel, blackened finish

GN 798.5

Retractable mechanism

- Stainless steel
- Stem, retaining pin, AISI 303
- Hub, AISI 316LHC, sintered

RoHS

Technical Information

Page

Plastic Characteristics QVX

Stainless Steel Characteristics QVX

Stepped retractable handles GN 798.3 / GN 798.5 are noted for their modern design, and the stepped shape provides the operator with a better grip.

Retractable handles are suitable when the handle must be withdrawn during automatic operations. The handle is pulled out of its taper seating in the direction of the arrow and then tilted. A compression spring locks the handle in both end positions.

A positive lock is achieved in the operating position by way of a tapered seating.

see also...

Page

GN 598.3 Retractable Handles (with Steel Locking Mechanism) QVX

GN 598.5 Retractable Handles (with Stainless Steel Locking Mechanism) QVX

How to order (Steel)

GN 798.3-KT-22

- 1 Material
- 2 Handle diameter d_1

How to order (Stainless steel)

GN 798.5-KT-25

- 1 Material
- 2 Handle diameter d_1

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

