



- 2** Type
- E For single joints
  - D For double joints

**Metric table**

Dimensions in: millimeters - inches

<b>d<sub>1</sub></b> Joint Ø	<b>d<sub>2</sub></b> Type E	<b>d<sub>3</sub></b> Type E	<b>d<sub>4</sub></b> Type D	<b>d<sub>5</sub></b> Type D	<b>l<sub>1</sub></b> Type E	<b>l<sub>2</sub></b> Type D
16 0.63	15 0.59	28 1.10	16 0.63	35 1.38	34 1.34	55 2.17
22 0.87	20.5 0.81	40 1.57	20 0.79	36 1.42	45 1.77	65 2.56
25 0.98	24.5 0.96	48 1.89	24 0.94	44 1.73	50 1.97	70 2.76
28 1.10	27.5 1.08	52 2.05	28 1.10	51 2.01	56 2.20	80 3.15
32 1.26	30.5 1.20	56 2.20	32 1.26	62 2.44	65 2.56	90 3.54
36 1.42	35.5 1.40	66 2.60	-	-	72 2.83	-
42 1.65	40 1.57	75 2.95	40 1.57	73 2.87	82 3.23	120 4.72
45 1.77	45 1.77	84 3.31	-	-	95 3.74	-
50 1.97	50 1.97	92 3.62	50 1.97	90 3.54	108 4.25	155 6.10
58 2.28	56 2.20	100 3.94	-	-	122 4.80	-

**Specification**

- Single joint boot
  - Type E
  - Neoprene rubber (CR)
  - Black
- Double joint boot
  - Type D
  - Smooth PVC elastomer plastic
  - Black
- RoHS compliant

**Information**

GN 808.1 cover boots provide universal joints protection against dirt, dust and other debris. They can also be filled with grease, which gives long term lubrication for friction bearings. The cover boots are secured at each end with two cable ties, supplied but not assembled.

see also...

- *Universal Joints with Friction Bearing DIN 808 (Steel, Plain Finish)*
- *Universal Joints with Friction Bearing DIN 808 (Stainless Steel)*

How to order <b>GN 808.1-25-E</b>	1 Joint diameter d <sub>1</sub>
	2 Type

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10