



SS Stainless Steel

4 Type

- B** With plastic knob, without lock nut
- BK** With plastic knob, with lock nut
- BN** With stainless steel knob, without lock nut
- BKN** With stainless steel knob, with lock nut

Specification

- Threaded body
Stainless steel AISI 316
Plunger pin chemically nickel plated
- Knob (Type B / BK)
Plastic
Technopolymer (Polyamide PA)
- Black, matte finish
- Not removable
- Knob (Type BN / BKN)
Stainless steel AISI 316
Not removable
- Spring
Stainless steel AISI 316Ti
- RoHS compliant



A4

Information

GN 818 indexing plungers are set apart by the materials used, allowing these plungers to withstand particularly corrosive environments.

see also...

- *List of Indexing Plunger Types*
- *Indexing Plungers GN 717 / GN 817 (Steel / Stainless Steel)*
- *Indexing Plungers GN 617 / GN 617.1 (Steel / Stainless Steel)*
- *Square Cam Action Spring Latches GN 722.1 (Steel / Stainless Steel)*
- *Mini Indexing Plungers GN 822.7 (Stainless Steel)*

How to order

GN 818-10-12-M16X1.5-BKN-A4

1	Pin diameter d_1
2	Stroke l_1
3	Thread d_2
4	Type
5	Material

Metric table

Dimensions in: millimeters - inches

1 d ₁ Pin -0.02 -0.05 Bore H7	2 l ₁	3 d ₂ Thread	d ₃	d ₄	k	l ₂	l ₃	l ₄	A/F	Spring load ≈	
										Initial	End
4 0.16	4 0.16	M 8 x 1	16 0.63	16 0.63	14 0.55	35 1.38	16 0.63	5 0.20	10 0.39	3.5 N 0.79 lbf	11 N 2.47 lbf
4 0.16	6 0.24	M 8 x 1	16 0.63	16 0.63	14 0.55	35 1.38	16 0.63	5 0.20	10 0.39	3 N 0.67 lbf	11 N 2.47 lbf
5 0.20	5 0.20	M 10 x 1	19 0.75	18 0.71	16 0.63	40 1.57	18 0.71	6 0.24	12 0.47	3 N 0.67 lbf	12 N 2.70 lbf
5 0.20	8 0.31	M 10 x 1	19 0.75	18 0.71	16 0.63	40 1.57	18 0.71	6 0.24	12 0.47	3 N 0.67 lbf	14 N 3.15 lbf
6 0.24	6 0.24	M 12 x 1.5	23 0.91	22 0.87	20 0.79	48 1.89	22 0.87	6 0.24	14 0.55	4.5 N 1.01 lbf	16 N 3.60 lbf
6 0.24	9 0.35	M 12 x 1.5	23 0.91	22 0.87	20 0.79	48 1.89	22 0.87	6 0.24	14 0.55	4 N 0.90 lbf	20 N 4.50 lbf
8 0.31	8 0.31	M 16 x 1.5	28 1.10	27 1.06	24 0.94	58 2.28	26 1.02	8 0.31	17 0.67	6 N 1.35 lbf	23 N 5.17 lbf
8 0.31	12 0.47	M 16 x 1.5	28 1.10	27 1.06	24 0.94	58 2.28	26 1.02	8 0.31	17 0.67	7 N 1.57 lbf	26 N 5.85 lbf
10 0.39	12 0.47	M 16 x 1.5	28 1.10	27 1.06	24 0.94	58 2.28	26 1.02	8 0.31	17 0.67	7.5 N 1.69 lbf	32 N 7.19 lbf
12 0.47	15 0.59	M 20 x 1.5	33 1.30	32 1.26	28.5 1.12	71.5 2.81	33 1.30	10 0.39	22 0.87	9 N 2.02 lbf	32 N 7.19 lbf