



Metric table

¹ d ₁	² d ₂ Bore diameter	d ₃	l ₁	l ₂ min.
22 0.87	B 8	18 0.71	85 3.35	60 2.36

Dimensions in: millimeters - inches

Specification

- Body
Plastic
Technopolymer (Polypropylene PP)
- Softline coating
Elastomer (TPE) 70 shore A
 - Chemically bonded with the plastic body
 - FDA compliant plastic granulate
 - Temperature resistant up to 176 °F (80 °C)
 - Black, matte finish
- ISO Fundamental Tolerances → page QVX
- Elastomer Characteristics → page QVX
- Plastic Characteristics → page QVX
- RoHS compliant

Information

The EN 819 cylindrical handle does not require a thread on the shaft.

During mounting, easy blows with a soft hammer are sufficient to drive the handle into place, the shaft end should be slightly rounded or chamfered (30°). The handle sits absolute vibration-tight.

The Softline coating makes them particularly ergonomic and easy to grip.

see also...

- Product Family Ergostyle® → page QVX
- Product Family Softline → page QVX

How to order ¹ ² EN 819-22-B8	1 Handle diameter d ₁
	2 Bore diameter d ₂