



ELESA original design MPE.



Metric table



Dimensions in: millimeters - inches

l_1	h_1	h_2	h_3	h_4	l_2	l_3	l_4	$m_1 \pm 0.1$	m_2
90	29	16.5	63	20	135	74	41	80	8
3.54	1.14	.65	2.48	.79	5.31	2.91	1.61	3.15	.31

Specification



- Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 212 °F (100 °C)
- Color (matte finish):
Black, RAL 9005 **SW**
Gray, RAL 7040 **GR**
White, RAL 9002, Cleanline **CL**
- Pin
Stainless steel
European Standard No. 1.4305 (AISI 303)
- Return spring
Stainless steel
European Standard No. 1.4319 (AISI 302)
- RoHS compliant

Information

EN 825.1 folding handles are used in applications where the handle must not protrude. After releasing the handle, it returns to its starting position by spring-loaded return.

see also...

- Product Range Cleanline
- Folding Handles GN 425.2 (Retained in Both End Positions)
- Folding Handles GN 425.5 (Retained in Both End Positions)
- Folding Handles with Recessed Tray EN 825.2 (Technopolymer Plastic, with Spring-Loaded Return)

On request

- Various metric size fasteners and kit packaging

How to order EN 825.1-90-SW	1 Length l_1
	2 Color