



ELESA original design MPE.



Metric table



Dimensions in: millimeters - inches

| l_1 | h_1 | h_2 | h_3 | h_4 | l_2 | l_3 | l_4 | $m_1 \pm 0.1$ | m_2 |
|-------|-------|-------|-------|-------|-------|-------|-------|---------------|-------|
| 90 | 29 | 16.5 | 63 | 20 | 135 | 74 | 41 | 80 | 8 |
| 3.54 | 1.14 | .65 | 2.48 | .79 | 5.31 | 2.91 | 1.61 | 3.15 | .31 |

Specification



- Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 212 °F (100 °C)
- Colors (matte finish):
Black, RAL 9005 **SW**
Gray, RAL 7040 **GR**
White, RAL 9002, Cleanline **CL**
- Pin
Stainless steel
European Standard No. 1.4305 (AISI 303)
- Return spring
Stainless steel
European Standard No. 1.4319 (AISI 302)
- RoHS compliant

Information

EN 825.1 folding handles are used in applications where the handle must not protrude. After releasing the handle, it returns to its starting position by spring-loaded return.

see also...

- *Folding Handles GN 425.2 (Retained in Both End Positions)*
- *Folding Handles GN 425.5 (Retained in Both End Positions)*
- *Folding Handles with Recessed Tray EN 825.2 (Technopolymer Plastic, with Spring-Loaded Return)*

On request

- Various metric size fasteners and kit packaging

| | |
|--|----------------|
| How to order   EN 825.1-90-SW | 1 Length l_1 |
| | 2 Color |