



Metric table

Dimensions in: millimeters / inches									
1 d ₁	2 d ₂ H7 Bore			d ₃	b	m	l ₁	l ₂ max. Type H	l ₃ max. Type S
40 1.57	B 8	B 10	-	4.3 0.17	16 0.63	28 1.10	30 1.18	50 1.97	27 1.06
50 1.97	B 8	B 10	B 12	5.3 0.21	16 0.63	36 1.42	30 1.18	56 2.20	32 1.26
60 2.36	B 10	B 12	-	5.3 0.21	16 0.63	44 1.73	30 1.18	61 2.40	36 1.42

Specification

Clamping element

Aluminum
Anodized finish, black

ELS

Wedge

Brass

Adjustable lever for type H

- Zinc die-cast
- Powder coated
- Black, RAL 9005, textured finish
- With set screw
- Stainless steel AISI 303

Set screw for type S

Stainless steel AISI 303

RoHS

Technical Information

Page

ISO Fundamental Tolerances	QVX
Stainless Steel Characteristics	QVX

Control knob flanges GN 826 are normally used in connection with control knobs and smaller handwheels.

When using these flanges, spindles can be clamped gently and easily, with little assembly and installation effort. The clamping wedge grips the spindle, preventing maladjustments caused by vibrations, or to keep the spindle securely in place after adjustment.

This flange can also be used to simply lock the spindle in place.

Flange may be mounted so that the clamping lever / clamping screw is positioned either on the left or the right hand side.

Indicator arrows GN 711.1 can be attached to the circumference of the control knob flange.

Accessory

GN 711.1 Indicator Arrows (with Self-Adhesive Backing)

QVX

How to order		1	Diameter d ₁
		2	Bore d ₂
		3	Type
		4	Finish
GN 826-40-B10-H-ELS			