



Metric



SS Stainless Steel

Metric table

1 d₁	2 l₁ Nominal length	3	Dimensions in: millimeters - <i>inches</i>												
			d ₂	d ₃	l ₂	l ₃ ± 0.3	A/F ₁	A/F ₂							
M 3	3 0.12	4 0.16	5 0.20	6 0.24	8 0.31	10 0.39	-	-	-	1.9 0.07	1.5 0.06	0.5 0.02	0.8 0.03	1.5	1.5
M 4	4 0.16	5 0.20	6 0.24	-	-	-	-	-	-	2.5 0.10	2 0.08	0.5 0.02	1 0.04	2	1.5
M 4	8 0.31	10 0.39	12 0.47	16 0.63	20 0.79	-	-	-	-	2.5 0.10	2 0.08	0.5 0.02	1 0.04	2	2
M 5	5 0.20	6 0.24	-	-	-	-	-	-	-	3 0.12	3 0.12	0.5 0.02	1 0.04	2.5	2
M 5	8 0.31	10 0.39	12 0.47	16 0.63	20 0.79	25 0.98	-	-	-	3 0.12	3 0.12	0.5 0.02	1 0.04	2.5	2.5
M 6	6 0.24	8 0.31	10 0.39	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	4 0.16	3.5 0.14	1 0.04	1.3	3
M 8	8 0.31	10 0.39	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	6 0.24	5 0.20	1.5 0.06	1.6 0.06	4
M 10	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	-	-	8 0.31	6.5 0.26	2 0.08	1.9 0.07	5
M 12	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	100 3.94	-	-	10 0.39	8 0.31	2 0.08	2.1 0.08	6

Specification

3

- Body
Stainless steel AISI 303

- Tip
 - Brass
 - Plastic (Polyacetal POM)

Information

GN 913.5 set screws with brass or plastic tip are used in applications where markings, pressure dents and damage to the workpiece are unacceptable.

see also...

- *Socket Set Screws GN 605 (with Flat Ball) → page 1104*

- *Stainless Steel Characteristics → page 2143*

- *Plastic Characteristics → page 2135*

- *RoHS compliant*

How to order

GN 913.5-M6-20-KU

1

2

3

1 Thread d₁2 Thread length l₁

3 Tip material