



2 Bore code

B Without keyway

4 Type

A Without handle

R With revolving handle

Specification



- Aluminum die-cast
 - Contact face of hub machined
 - Rim turned
 - Powder coated
 - Black, RAL 9005, textured finish **SW**
 - Silver, RAL 9006, textured finish **SR**
- Radial and axial runout of the rim < 0.4 mm
- Stepped cylindrical revolving handle GN 798.2
 - Plastic Technopolymer
 - Black, matte finish
 - Threaded spindle
 - Steel, zinc plated, blue passivated finish
- Keyways *WN / DIN 6885*
- Cross Holes *GN 110*
- *ISO Fundamental Tolerances*
- **RoHS compliant**

Accessory

- Countersunk washers GN 184

On request

- Other modifications such as special inch and metric bores, keyways, set screw holes, etc.

Information

GN 924 flat-faced spoked handwheels are distinguished by their modern design.

The removable plastic cover shrouds the mounting components such as screws, countersunk washers as well as the shaft end.

No mounting hole in rim for handwheel without handle. Handle shipped loose; mounting of handle is required.

see also...

- *Two Spoked Handwheels GN 322 (Aluminum, Rim Highly Polished)*

<p>How to order (Inch)</p> <p>GN 924-140-B5/8-A-SW</p>	1 Handwheel diameter d_1
	2 Bore code
	3 Bore diameter d_2
	4 Type
	5 Color

<p>How to order (Metric)</p> <p>GN 924-200-B18-R-SR</p>	1 Handwheel diameter d_1
	2 Bore code
	3 Bore diameter d_2
	4 Type
	5 Color

Inch table


Dimensions in: inches - *millimeters*

d₁	d₂ +0.001 Bore	d₃	d₄	b	h	l₁	l₂ ≈	l₃ ≈	r	Ø Handle GN 798.2	Recommended countersunk washer
4.92 <i>125</i>	1/2	1.22 <i>31</i>	0.91 <i>23</i>	0.59 <i>15</i>	0.43 <i>11</i>	0.71 <i>18</i>	1.32 <i>33.5</i>	2.42 <i>61.5</i>	1.79 <i>45.5</i>	0.87 <i>22</i>	184-20
5.51 <i>140</i>	5/8	1.42 <i>36</i>	1.12 <i>28.5</i>	0.65 <i>16.5</i>	0.51 <i>13</i>	0.75 <i>19</i>	1.44 <i>36.5</i>	3.01 <i>76.5</i>	2.05 <i>52</i>	0.94 <i>24</i>	184-25
6.30 <i>160</i>	5/8	1.42 <i>36</i>	1.12 <i>28.5</i>	0.71 <i>18</i>	0.57 <i>14.5</i>	0.79 <i>20</i>	1.56 <i>39.5</i>	3.01 <i>76.5</i>	2.40 <i>61</i>	0.94 <i>24</i>	184-25
7.87 <i>200</i>	3/4	1.65 <i>42</i>	1.42 <i>36</i>	0.81 <i>20.5</i>	0.63 <i>16</i>	0.94 <i>24</i>	1.79 <i>45.5</i>	3.35 <i>85</i>	3.05 <i>77.5</i>	0.98 <i>25</i>	184-32

Metric table


Dimensions in: millimeters - *inches*

d₁	d₂ H7 Bore		d₃	d₄	b	h	l₁	l₂ ≈	l₃ ≈	r	Ø Handle GN 798.2	Recommended countersunk washer
125 <i>4.92</i>	12	14	31 <i>1.22</i>	23 <i>0.91</i>	15 <i>0.59</i>	11 <i>0.43</i>	18 <i>0.71</i>	33.5 <i>1.32</i>	61.5 <i>2.42</i>	45.5 <i>1.79</i>	22 <i>0.87</i>	184-20
140 <i>5.51</i>	14	16	36 <i>1.42</i>	28.5 <i>1.12</i>	16.5 <i>0.65</i>	13 <i>0.51</i>	19 <i>0.75</i>	36.5 <i>1.44</i>	76.5 <i>3.01</i>	52 <i>2.05</i>	24 <i>0.94</i>	184-25
160 <i>6.30</i>	14	16	36 <i>1.42</i>	28.5 <i>1.12</i>	18 <i>0.71</i>	14.5 <i>0.57</i>	20 <i>0.79</i>	39.5 <i>1.56</i>	76.5 <i>3.01</i>	61 <i>2.40</i>	24 <i>0.94</i>	184-25
200 <i>7.87</i>	18	20	42 <i>1.65</i>	36 <i>1.42</i>	20.5 <i>0.81</i>	16 <i>0.63</i>	24 <i>0.94</i>	45.5 <i>1.79</i>	85 <i>3.35</i>	77.5 <i>3.05</i>	25 <i>0.98</i>	184-32