



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

d	b ₁	b ₂	h ₁	h ₂	h ₃	Length l	r ₁	r ₂	s	Stroke cam	r ₂ -h ₃ Total stroke
8 .31	13 .51	9 .35	19.54 .77	14 .55	12 .47	114 4.49	17.2 .68	21.07 .83	3.87 .15	9.07 .36	
10 .39	17 .67	12 .47	24.54 .97	17 .67	15 .59	138 5.43	21.6 .85	26.45 1.04	4.85 .19	11.45 .45	
12 .47	20 .79	14 .55	31.81 1.25	21 .83	18 .71	157 6.18	28 1.10	34.29 1.35	6.29 .25	16.29 .64	

Specification

- **GN 917**
Lever body
Steel
ST 52-3 / German Material No. 1.0570
Blackened finish
 - **GN 917.1**
Lever body
Stainless steel
European Standard No. 1.4301 (AISI 304)
Shot-blasted finish
- This information applies to both series:
- King pin
Stainless steel
European Standard No. 1.4021 (AISI 420)
Tempered
 - Snap ring
Stainless steel
European Standard No. 1.4310 (AISI 301)
 - Plastic cap
- High quality, oil resistant red plastic
- Temperature resistant up to 140 °F (60 °C)
 - RoHS compliant

Information

GN 917 / GN 917.1 double cam levers are used for repositioning and clamping.
The eccentrical cam has the advantage that the clamping force remains constant in every position of movement. It is also self-locking.
Dimension b₂ is made to match the head size of eye bolts DIN 444 and eye nuts GN 444.2 respectively.
Hubs with eccentrical cam, see GN 919.
see also...

- *Swing Bolts DIN 444*
- *Eye Nuts DIN 444.2*
- *Eccentrical Cam Units GN 918*

How to order (Steel) GN 917-10-17	1 Diameter d
	2 Width b ₁

How to order (Stainless steel) GN 917.1-12-20	1 Diameter d
	2 Width b ₁