


**SS** Stainless Steel

**3** Type

- MS** Brass tip
- KU** Plastic tip (Polyacetal POM)
- ZK** Ball end



**Metric table**

<b>1</b> d <sub>1</sub> Thread	<b>2</b> l <sub>1</sub> Nominal length					d <sub>2</sub>	d <sub>3</sub>	d <sub>4</sub> +0.05	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub>	l <sub>5</sub> ≈	A/F
M 6	16*	20	25	30	35	4	3.5	4.5	1	1.3	4	5.1	10
	0.63	0.79	0.98	1.18	1.38	0.16	0.14	0.18	0.04	0.05	0.16	0.20	0.39
M 8	20*	25	30	35	45	6	5	6.1	1.5	1.6	5.3	6.2	13
	0.79	0.98	1.18	1.38	1.77	0.24	0.20	0.24	0.06	0.06	0.21	0.24	0.51
M 10	25*	30	35	45	55	8	6.5	7.8	2	1.9	6.4	7.3	17
	0.98	1.18	1.38	1.77	2.17	0.31	0.26	0.31	0.08	0.07	0.25	0.29	0.67

Dimensions in: millimeters - inches

\* Only available in type MS and KU

**Specification**

- Stainless steel AISI 304
- *Stainless Steel Characteristics* → page QVX
- *Plastic Characteristics* → page QVX
- RoHS compliant

**Information**

GN 933.5 hex head screws with brass or plastic tip are used in applications where markings, pressure dents and damage to the workpiece are unacceptable.

The type ZK has a ball diameter d<sub>4</sub> that is smaller than the core diameter d<sub>1</sub> of the thread. This makes it suitable for use with GN 631 / GN 631.5 thrust pads which need to be ordered separately.

see also...

- *Set Screws GN 913.5 (Stainless Steel)* → page QVX
- *Thrust Pads GN 631 (Plastic)* → page QVX
- *Thrust Pads GN 631.5 (Stainless Steel)* → page QVX

<p>How to order</p> <p><b>GN 933.5-M6-20-KU</b></p>	<b>1</b> Thread d <sub>1</sub>
	<b>2</b> Thread length l <sub>1</sub>
	<b>3</b> Type