




Metric table

1

2

Dimensions in: millimeters - inches

b	d ₁ ^{+0.06} / _{+0.02} Bore					d ₂	l ₁	l ₂	l ₃	l ₄	m ₁	m ₂	For position indicator
33 1.30	B 8	B 10	B 12	B 14	-	4.5 0.18	47 1.85	30.5 1.20	11 0.43	22 0.87	21 0.83	23.5 0.93	EN 954 / EN 9054
48 1.89	B 12	B 14	B 15	B 16	B 20	5.5 0.22	67 2.64	43.1 1.70	16 0.63	22 0.87	34 1.34	33.6 1.32	EN 953

Specification

- Body
Zinc die-cast
Powder coated
Black, textured finish
- Straight adjustable lever GN 302-30
Black, RAL 9005, textured finish
→ page 454
- RoHS compliant

Information

GN 953.6 and GN 954.6 clamping plates are used in connection with EN 953, EN 954 and EN 9054 position indicators. The mounting holes support typical hole patterns.

After installation and adjustment of the spindles, they can easily be clamped and locked.

At the same time these plates include bore size Ø 6.1 mm to accept the torque limiter for the position indicator.

The clamping plate can be installed so that the adjustable lever is positioned either to the right or the left.

How to order (For EN 953) 12 GN953.6-48-B20	1	Width b
	2	Bore d ₁
How to order (For EN 954 / EN 9054) 12 GN954.6-33-B10	1	Width b
	2	Bore d ₁