



Metric table

Dimensions in: millimeters - *inches*

d₁ ±0.2	Length l ±0.25						d₂	For self-tapping screws DIN 7500
20 <i>0.79</i>	194 <i>7.64</i>	244 <i>9.61</i>	294 <i>11.57</i>	394 <i>15.51</i>	-	-	4.5 <i>0.18</i>	M 5
28 <i>1.10</i>	192 <i>7.56</i>	242 <i>9.53</i>	292 <i>11.50</i>	392 <i>15.43</i>	492 <i>19.37</i>	592 <i>23.31</i>	5.5 <i>0.22</i>	M 6
30 <i>1.18</i>	189 <i>7.44</i>	289 <i>11.38</i>	389 <i>15.31</i>	489 <i>19.25</i>	589 <i>23.19</i>	989 <i>38.94</i>	3.6 <i>0.14</i>	M 4

Specification

- Aluminum
 - Powder coated
 - Black, RAL 9005, textured finish (available up to 3000 mm length) **● SW**
 - Anodized finish, natural color (available up to 2600 mm length) **● EL**
- RoHS compliant

Information

GN 930 handle tubes with screw channel are designed for use in a variety of different tube handles (e.g. GN 333).

For applications not requiring handle bases, the screw channel provides a very economical mounting solution by using self-tapping screws. The lengths, dimension "l" listed in the table are stock lengths.

see also...

- Tubular Handles GN 333* → page QVX
- Angled Handle Legs GN 333.8 (for Tubular Handles Ø 28 mm)* → page QVX
- Straight Handle Legs GN 333.9 (for Tubular Handles Ø 28 mm)* → page QVX

On request

- Plastic cover in black or light gray for tube Ø 28 mm
- Any lengths below 3000 mm

How to order GN 930-30-989-EL	1 Handle diameter d ₁
	2 Length l
	3 Finish