




Application example



ELESA original design NCD



Metric table



Dimensions in: millimeters - inches

A/F	d ₀ For DIN nuts or bolts	d ₁	d ₂	h ₁	h ₂	h ₃	t ≈ max.
7	M 4	9 <i>0.35</i>	6.9 <i>0.27</i>	7.8 <i>0.31</i>	3.5 <i>0.14</i>	6.5 <i>0.26</i>	5 <i>0.20</i>
8	M 5	10.9 <i>0.43</i>	7.9 <i>0.31</i>	10.4 <i>0.41</i>	6 <i>0.24</i>	9.3 <i>0.37</i>	7 <i>0.28</i>
10	M 6	12.9 <i>0.51</i>	9.8 <i>0.39</i>	12.4 <i>0.49</i>	7 <i>0.28</i>	11.4 <i>0.45</i>	9 <i>0.35</i>
13	M 8	16.3 <i>0.64</i>	12.8 <i>0.50</i>	15 <i>0.59</i>	8.5 <i>0.33</i>	14 <i>0.55</i>	12 <i>0.47</i>
17	M 10	20.3 <i>0.80</i>	16.7 <i>0.66</i>	19.1 <i>0.75</i>	9 <i>0.35</i>	17.2 <i>0.68</i>	14 <i>0.55</i>
19	M 12	22.6 <i>0.89</i>	18.7 <i>0.74</i>	20 <i>0.79</i>	10.1 <i>0.40</i>	17.9 <i>0.70</i>	15 <i>0.59</i>
22	M 14	27 <i>1.06</i>	21.7 <i>0.85</i>	23.5 <i>0.93</i>	11.5 <i>0.45</i>	22 <i>0.87</i>	19 <i>0.75</i>
24	M 16	29.2 <i>1.15</i>	23.7 <i>0.93</i>	26 <i>1.02</i>	14.6 <i>0.57</i>	24 <i>0.94</i>	20 <i>0.79</i>
30	M 20	35.7 <i>1.41</i>	29.8 <i>1.17</i>	32.8 <i>1.29</i>	17.9 <i>0.70</i>	30.2 <i>1.19</i>	26 <i>1.02</i>
36	M 24	44 <i>1.73</i>	35.8 <i>1.41</i>	40 <i>1.57</i>	20 <i>0.79</i>	37.6 <i>1.48</i>	33 <i>1.30</i>
46	M 30	55.1 <i>2.17</i>	45.8 <i>1.80</i>	50.2 <i>1.98</i>	24.5 <i>0.96</i>	47.7 <i>1.88</i>	42 <i>1.65</i>

Specification



- Plastic
Technopolymer (Polyethylene PE)
- Temperature resistant up to 176 °F (80 °C)
- Black, RAL 9005, matte finish ● **SW**
- RoHS compliant

Information

EN 934.1 domed cover caps are designed for hexagon nut and bolt sizes according to DIN 933 / DIN 934.

They protect from dirt and corrosion and attractively cover projecting bolts and nuts. Moreover, they reduce the danger of injury from sharp edges.

The cover caps can be mounted by hand or using a soft-head hammer.

On request

- Cover caps with other wrench sizes
- Chrome plated plastic

How to order	
EN 934.1-10-SW	1 Across flats A/F
	2 Color

