



ELESA original design VRU. / VRU +I

2 Bore code

B Without keyway

4 Type

A Without handle

D With revolving handle

Universal table

Dimensions in: millimeters - inches

d ₁	d ₂ H9 Bore	d ₃	d ₆	b	l ₁	l ₂	l ₃	l ₄	l ₅	d ₄	d ₅
125 4.92	10 .39	55 2.17	32 1.26	18 .71	15 .59	22 .87	28 1.10	65 2.56	47 1.85	23 .91	M 8
160 6.30	10 .39	70 2.76	42 1.65	22 .87	17 .67	26 1.02	35 1.38	65 2.56	60 2.36	23 .91	M 8
200 7.87	12 .47	85 3.35	53 2.09	26 1.02	20 .79	27 1.06	40 1.57	80 3.15	75 2.95	26 1.02	M 10
250 9.84	12 .47	105 4.13	68 2.68	30 1.18	22 .87	30 1.18	49 1.93	80 3.15	99 3.90	26 1.02	M 10

Specification

- Plastic
Duroplast
(Phenolic PF)
- High strength reinforced
- Black, glossy finish
- Hub bushing
Steel, blackened finish, molded-in
- Revolving handles
Plastic, Duroplast
- Black, glossy finish
- Threaded spindle
Steel, zinc plated
- Both dimensions, inch and metric, are interchangeable
- RoHS compliant

Information

EN 940 three spoked handwheels are resistant to solvents, oils, grease and other chemical agents. No mounting hole in rim for handwheel without handle. Handle shipped loose; mounting of handle is required.

see also...

- Three Spoked Handwheels EN 950

On request

- Other modifications such as special inch and metric bores, keyways, set screw holes, etc.

How to order

EN 940-125-B10-A

1	Handwheel diameter d ₁
2	Bore code
3	Bore diameter d ₂
4	Type