



ELESA original design RB51 / RB52 / RB50



Metric table

1		2						3			Dimensions in: millimeters - inches
d ₁ f7	d ₂ H7 Bore						l ₁	d ₃	l ₂	For position indicators	
10 0.39	B 6	B 8	-	-	-	-	20 0.79	3.2 0.13	2.5 0.10	EN 955	
14 0.55	B 6	B 8	B 10	B 12	-	-	20 0.79	4.25 0.17	3.5 0.14	EN 954 / EN 9054	
20 0.79	B 6	B 8	B 10	B 12	B 14	B 15	B 16	20 0.79	5.5 0.22	4.5 0.18	EN 953 / EN 9053 / EN 9153

Specification

- Steel, blackened finish —
- Stainless steel **NI**
European Standard No 1.4301 (AISI 304)
- RoHS compliant

Information

EN 952.1 mounting adaptors are used to adapt position indicators to accept different smaller spindle diameters.

Adaptors are supplied with a set screw.

see also...

- Digital Position Indicators EN 953
- Digital Position Indicators EN 954
- Digital Position Indicators EN 955
- Digital Position Indicators EN 9053
- Digital Position Indicators EN 9054
- Digital Position Indicators EN 9153

How to order (Steel)	1	Outside diameter d ₁
EN 952.1-14-B12-20	2	Bore d ₂
	3	Length l ₁

How to order (Stainless steel)	1	Outside diameter d ₁
EN 952.1-10-B8-20-NI	2	Bore d ₂
	3	Length l ₁
	4	Material