



**3 Type**

- D** With plain shaft
- E** With threaded shaft

**Metric table**



Dimensions in: millimeters - *inches*

d <sub>1</sub>	d <sub>2</sub> h8 Type D		d <sub>3</sub> Type E		d <sub>4</sub> h13	l <sub>1</sub> ≈	l <sub>2</sub>	l <sub>3</sub>	A/F Internal hexagon
	ST / AL	KT	ST / AL	KT					
16 <i>0.63</i>	7 <i>0.28</i>	7 <i>0.28</i>	M 6	M 6	10 <i>0.39</i>	49 <i>1.93</i>	11 <i>0.43</i>	5.5 <i>0.22</i>	3
20 <i>0.79</i>	8 <i>0.31</i>	8 <i>0.31</i>	M 8	M 8	13 <i>0.51</i>	61 <i>2.40</i>	13 <i>0.51</i>	6 <i>0.24</i>	4
25 <i>0.98</i>	10 <i>0.39</i>	10 <i>0.39</i>	M 10	M 10	16 <i>0.63</i>	75 <i>2.95</i>	14 <i>0.55</i>	8 <i>0.31</i>	5
32 <i>1.26</i>	13 <i>0.51</i>	13 <i>0.51</i>	M 12	M 12	20 <i>0.79</i>	95 <i>3.74</i>	21 <i>0.83</i>	10.5 <i>0.41</i>	6
36 <i>1.42</i>	16 <i>0.63</i>	-	M 16	-	22 <i>0.87</i>	106 <i>4.17</i>	26 <i>1.02</i>	11 <i>0.43</i>	8

**Specification**



- Steel, zinc plated, blue passivated finish **ST**
- Aluminum **AL**  
Turned and polished
- Plastic **KT**  
Technopolymer (Polyamide PA)  
- Temperature resistant up to 230 °F (110 °C)  
- Black, matte finish
- Spindle  
Steel, zinc plated, blue passivated finish
- RoHS compliant

**Information**

DIN 98 revolving handles have a comfortable grip and are widely used on crank handles or handwheels. Type D handles are supplied unassembled so that the shaft can be press-fit or screwed into a tapped blind bore prior to assembly. During mounting, easy blows with a soft mallet are sufficient to drive the handle into place.

<p>How to order</p> <p><b>DIN 98-KT-20-E</b></p>	<b>1</b>	<b>Material</b>
	<b>2</b>	<b>Handle diameter d<sub>1</sub></b>
	<b>3</b>	<b>Type</b>