



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

| 1 | | | 2 | | | | |
|----------------|---------------------|----------------------|----------------|----------------|----------------|------------------|--------------|
| d ₁ | | | d ₂ | d ₃ | h ₁ | h ₂ ≈ | Length l ≈ |
| GN 99.7 | GN 99.8 AISI 304 | GN 99.8 AISI 316L | Thread | | | | |
| 16 .63 | 16 .63 | 16 .63 | M 8 | 10 .39 | 12.5 .49 | 26 1.02 | 47.5 1.87 |
| 20 .79 | 20 .79 | 20 .79 | M 10 | 12 .47 | 15 .59 | 32 1.26 | 59.5 2.34 |
| 25 .98 | 25 .98 | 25 .98 | M 12 | 14 .55 | 19 .75 | 40 1.57 | 75.5 2.97 |
| 32 1.26 | 32 1.26 | - | M 16 | 18 .71 | 25 .98 | 52 2.05 | 94.5 3.72 |
| 40 1.57 | 40 1.57 | - | M 20 | 20 .79 | 31 1.22 | 62 2.44 | 118 4.65 |

Specification

- **GN 99.7**
Steel, zinc plated, blue passivated finish —
- **GN 99.8**
Stainless steel, matte shot-blasted finish
- European Standard No. 1.4301 (AISI 304) —
- European Standard No. 1.4404 (AISI 316L) **A4**
- Clamp arms
Butt-welded to tapped hub
- **RoHS compliant**

Information

Latest production techniques make these GN 99.7 and GN 99.8 double arm clamp nuts an extremely good value.

see also...

- Double Arm Clamp Nuts GN 206.1 (Malleable Iron)
- Double Arm Clamp Nuts GN 206.1 (Stainless Steel)

On request

- Special inch and metric bores or threads

| | |
|---|---------------------------|
| How to order (Steel) 1 2 GN 99.7-20-M10 | 1 Diameter d ₁ |
| | 2 Thread d ₂ |
| How to order (Stainless steel AISI 304) 1 2 GN 99.8-32-M16 | 1 Diameter d ₁ |
| | 2 Thread d ₂ |
| How to order (Stainless steel AISI 316L) 1 2 3 GN 99.8-25-M12-A4 | 1 Diameter d ₁ |
| | 2 Thread d ₂ |
| | 3 Material |

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4