

Universal



elesa
Original design VR.FP / VR.FP +I

- 2


Bore code
- BLANK

Without bore
- 3

Type
- A

Without handle
- D

With revolving handle



Universal table

d ₁	Bore	d ₂	d ₃	b	l ₁	l ₂	l ₃	l ₄	l ₅	d ₄	d ₅
3.94 100	Blank	0.94 24	0.79 20	0.55 14	1.42 36	0.47 12	1.57 40	1.57 40	1.46 37	0.71 18	M 6
4.92 125	Blank	0.94 24	0.79 20	0.71 18	1.42 36	0.47 12	1.77 45	1.97 50	1.85 47	0.83 21	M 8
6.30 160	Blank	1.26 32	0.94 24	0.87 22	1.50 38	0.59 15	1.97 50	2.56 65	2.32 59	0.91 23	M 8
7.09 180	Blank	1.57 40	1.22 31	0.94 24	1.69 43	0.59 15	2.20 56	3.15 80	2.68 68	1.02 26	M 10
7.87 200	Blank	1.57 40	1.22 31	0.94 24	1.69 43	0.59 15	2.20 56	3.15 80	2.99 76	1.02 26	M 10
9.84 250	Blank	1.93 49	1.50 38	1.18 30	1.73 44	0.59 15	2.60 66	3.54 90	3.86 98	1.10 28	M 10
11.42 290	Blank	2.28 58	1.85 47	1.26 32	2.20 56	0.71 18	3.07 78	3.94 100	4.45 113	1.22 31	M 12
14.76 375	Blank	2.28 58	2.28 58	1.57 40	3.03 77	1.02 26	4.25 108	3.94 100	6.30 160	1.22 31	M 14

Specification

Body

- Plastic, Phenolic (PF)
- High strength reinforced
- Black, shiny finish

Hub bushing

- Steel, blackened finish

Revolving handle

- Plastic, Phenolic (PF)
- Black, shiny finish
- Threaded spindle
- Steel, zinc plated

RoHS

On request

- Other modifications such as inch and metric bores, keyways, set screw holes, etc

Three spoked handwheels EN 950 are resistant to solvents, oils, grease and other chemical agents.

Technical Information	Page
Plastic Characteristics	QVX

Accessory	
GN 184 Countersunk Washers (for Axial Fixing)	QVX

How to order	
1 Handwheel diameter d ₁	
2 Bore code	
3 Type	
EN 950-180-BLANK-D	