



Metric table

Dimensions in: millimeters - inches

b	d₁ F9 Bore	d₂	l₁	l₂	l₃	l₄	l₅	m₁	m₂	m₃	m₄
33 1.30	B 8 B 10 B 12 B 14	4.5 0.18	47 1.85	30.5 1.20	9.5 0.37	24.5 0.96	22 0.87	20 0.79	21 0.83	23.5 0.93	20 0.79

Specification

- Zinc die-cast
Powder coated
Black, textured finish
- Adjustable lever GN 302.1 → page QVX
 - Zinc die-cast
Powder coated
Black, RAL 9005, textured finish
 - Threaded stud
Stainless steel AISI 303
- ISO Fundamental Tolerances → page QVX
- Stainless Steel Characteristics → page QVX
- RoHS compliant

Information

Clamping plates GN 954.7 are used in connection with position indicators EN 954 / EN 954.2. The mounting holes support typical bore hole patterns.

In a simpler manner and without great construction and installation effort these spindles can, after adjustment, be clamped and locked.

At the same time these plates are fitted with bore diameter 6.1 to accommodate the torque support of the position indicator.

The clamping plate can be installed so that the hand lever is situated as required either on the right or the left.

see also...

- Digital Position Indicators EN 954 (Steel Shaft Receptacle) → page QVX
- Digital Position Indicators EN 954.2 (Stainless Steel Shaft Receptacle) → page QVX

How to order

GN954.7-33-B10

1 Width b

2 Bore d₁