



SS Stainless Steel

3 Type

- K** Straight lever with plain bore (only steel version)
- M** Straight lever with tapped bore (only steel version)
- L** Angled lever with plain bore
- N** Angled lever with tapped bore

Metric table

Dimensions in: millimeters - inches

l ₁	Steel				Stainless Steel		b	d ₃	d ₄ ≈	d ₅ -0.2	h ≈	l ₂ ≈	
	d ₁ Thread	Type M	Type N	d ₂ H7 Bore	Type K	Type L							d ₁ Thread
50 1.97	M 6	M 6	M 6	B 6	B 6	M 6	-	9.5 .37	8 .31	7.5 .30	12 .47	24 .94	48 1.89
63 2.48	M 8	M 8	M 8	B 8	B 8	M 8	B 8	12 .47	10 .39	11 .43	16 .63	30.5 1.20	60 2.36
80 3.15	M 10	M 10	M 10	B 10	B 10	M 10	B 10	14.5 .57	13 .51	15 .59	20 .79	38 1.50	76 2.99
100 3.94	M 12	M 12	M 12	B 12	B 12	M 12	B 12	18.5 .73	16 .63	19 .75	25 .98	47 1.85	95 3.74
125 4.92	M 16	M 16	M 16	B 16	B 16	M 16	-	24 .94	20 .79	23.5 .93	32 1.26	59.5 2.34	119 4.69
160 6.30	M 20	M 20	M 20	B 20	B 20	-	-	30 1.18	25 .98	29.5 1.16	40 1.57	76 2.99	152 5.98
200 7.87	-	M 24	M 24	-	B 24	-	-	40 1.57	32 1.26	33 1.30	50 1.97	97 3.82	190 7.48

Specification

- Steel —
- Turned
- Blackened finish
- Stainless steel **NI**
European Standard No. 1.4305 (AISI 303),
matte shot-blasted finish
- RoHS compliant

Information

DIN 99 fixed clamping levers are machined from solid bar. Ideal for applications that require higher levels of torque.

see also...

- *Clamp Nuts GN 99.5 (Steel)*
- *Clamp Nuts GN 99.6 (Stainless Steel)*
- *Adjustable Clamping Levers GN 99.2 (Steel, Blackened Finish)*

On request

- Stainless steel clamping levers with straight lever
- Special inch and metric bores or threads

How to order (Steel)

DIN 99-100-M12-N

1	Lever length l ₁
2	Thread d ₁ (Bore d ₂)
3	Type

How to order (Stainless steel)

DIN 99-63-M8-N-NI

1	Lever length l ₁
2	Thread d ₁ (Bore d ₂)
3	Type
4	Material