



- 4 Type**
- N With plastic pad (only for MIG)
 - E With rubber pad (only for MIG-EL)

Specification

- Threaded stud
Steel, zinc plated, blue passivated finish
- Base
Steel, nickel plated
- **MIG**
Plastic pad
Nylon
- **MIG-EL**
Rubber pad
Elastomer, non-skid
- RoHS compliant

On request

- Stainless steel version

Information

MIG and MIG-EL "Glide-Rite"™ industrial glides are an economical way of leveling light duty machines, cabinets, office furniture, or any type of light weight equipment. The steel with nickel plating provides a very decorative finish that is acceptable for all applications. The nylon pad is non-abrasive to the surface in which it is placed. The elastomer pad provides greater stability for non-skid applications, reduces noise, shock and vibration, and is oil resistant.

A coupling nut is not recommended to use for installation. Use a nut or tapped hole of 1 - 1 1/2 times the thread diameter of the threaded stud.

To insure a proper glide size, divide the machine weight by the number of mounts required. This will equal the pounds or load per mount.

see also...

- "Glide-Rite"™ Industrial Glides IIG / IIG-EL (Inch Size) → page 1494

How to order (MIG)	1 Base diameter d ₁
1 2 3 4	2 Thread d ₂
MIG-1.20-M6-1.50-N	3 Stud length l ₁
	4 Type
How to order (MIG-EL)	1 Base diameter d ₁
1 2 3 4	2 Thread d ₂
MIG-EL-2.40-M10-4.00-E	3 Stud length l ₁
	4 Type

Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂ Thread	³ l ₁	l ₂	l ₃	l ₄	A/F	Max. load
30.5 1.20	M 6	38.1 1.50	19.1 0.75	9.5 0.374	3.5 0.138	5.0	1112.05 N 250 lbf
30.5 1.20	M 8	38.1 1.50	19.1 0.75	9.5 0.374	3.5 0.138	6.0	1112.05 N 250 lbf
51.6 2.03	M 8	38.1 1.50	25.1 0.99	12.4 0.488	5.4 0.213	6.0	1112.05 N 250 lbf
51.6 2.03	M 10	50.8 2.00	25.1 0.99	12.4 0.488	5.4 0.213	8.0	1112.05 N 250 lbf
61.0 2.40	M 10	50.8 2.00	26.2 1.03	14.0 0.551	5.4 0.213	8.0	1112.05 N 250 lbf
61.0 2.40	M 10	101.6 4.00	26.2 1.03	14.0 0.551	5.4 0.213	8.0	1112.05 N 250 lbf
61.0 2.40	M 12	50.8 2.00	26.2 1.03	14.0 0.551	5.4 0.213	10.0	1112.05 N 250 lbf
61.0 2.40	M 12	101.6 4.00	26.2 1.03	14.0 0.551	5.4 0.213	10.0	1112.05 N 250 lbf
71.1 2.80	M 12	50.8 2.00	26.9 1.06	14.2 0.559	5.4 0.213	10.0	2224.11 N 500 lbf
71.1 2.80	M 12	101.6 4.00	26.9 1.06	14.2 0.559	5.4 0.213	10.0	2224.11 N 500 lbf
71.1 2.80	M 16	50.8 2.00	26.9 1.06	14.2 0.559	5.4 0.213	13.0	2224.11 N 500 lbf
71.1 2.80	M 16	101.6 4.00	26.9 1.06	14.2 0.559	5.4 0.213	13.0	2224.11 N 500 lbf
81.0 3.19	M 12	101.6 4.00	29.2 1.15	15.8 0.622	5.4 0.213	10.0	2224.11 N 500 lbf
81.0 3.19	M 12	152.4 6.00	29.2 1.15	15.8 0.622	5.4 0.213	10.0	2224.11 N 500 lbf
81.0 3.19	M 16	101.6 4.00	29.2 1.15	15.8 0.622	5.4 0.213	13.0	2224.11 N 500 lbf
81.0 3.19	M 16	152.4 6.00	29.2 1.15	15.8 0.622	5.4 0.213	13.0	2224.11 N 500 lbf