



- 4 Type
- M Straight lever
- N Angled lever

Metric table

1	2	3	Dimensions in: millimeters / inches											
d ₁	d ₂	l ₁						d ₃	d ₄	h ₁	h ₂	h ₃ ≈	l ₂	l ₃ ≈
10 0.39	M 8	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	13.5 0.53	20 0.79	25 0.98	8 0.31	39.5 1.56	63 2.48	60 2.36
13 0.51	M 10	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	16 0.63	25 0.98	29 1.14	8 0.31	49.5 1.95	80 3.15	76 2.99
16 0.63	M 12	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	19 0.75	28 1.10	33.5 1.32	10.5 0.41	60.5 2.38	100 3.94	95 3.74

Specification

- Hub / Shaft
- Steel, blackened finish
- Threaded stud
- Steel, blackened finish
- Property class 5.8
- RoHS

Adjustable clamping levers GN 99.2 are known for their small dimensions. They are used in applications where either the clamping range is limited, or a specific lever position is required. The serrated bore in the spherical hub is fitted with a insert which engages in the hub with its own serrations. By depressing the clamping lever the serrations are disengaged, freeing it for repositioning in the most convenient position. When the lever is released, the serrations will re-engage automatically. Should a rotation of 360° not be possible, the insert can be slightly screwed in (after the lever has been disengaged) by means of the slotted knurled screw.

Technical Information	Page
Strength Values of Screws	QVX