



3 Type

D With revolving retractable handle

Universal table

Dimensions in: millimeters - inches

1	2												
d_1	d_2 Pilot hole	d_3	d_4	b	s	l_1	l_2	l_3	l_4	l_5	l_6	d_5	
100 3.94	P 4	24 .94	21 .83	20 .79	15 .59	24 .94	12 .47	46 1.81	52 2.05	98 3.86	50 1.97	M 4	
125 4.92	P 6	24 .94	21 .83	24 .94	17 .67	28 1.10	12 .47	51 2.01	52 2.05	103 4.06	54 2.13	M 4	
160 6.30	P 6	32 1.26	23 .91	28 1.10	20 .79	31 1.22	15 .59	61 2.40	72 2.83	133 5.24	65 2.56	M 5	
200 7.87	P 6	40 1.57	26 1.02	32 1.26	24 .94	40 1.57	15 .59	74 2.91	92 3.62	166 6.54	79 3.11	M 6	

Specification

- Nylon plastic
 - Glass filled
 - Temperature resistant up to 230 °F (110 °C)
 - Black, matte finish
- Hub bushing
 - Steel, zinc plated, molded-in
- Revolving retractable handles PGR
 - Nylon plastic
 - Black, matte finish
 - Retractable mechanism
 - Chrome plated steel hub
 - Zinc plated steel stem
- RoHS compliant

Information

SHA-MRP handwheels with revolving retractable handle are distinguished by their modern design. By pulling up on the handle 90°, the handle locks into the rotating position. Disengage the handle by pulling it out and moving it down 90° back to the center of the handwheel. A compression spring secures the handle in either position.

These handwheels are an excellent choice for applications requiring the handle to be kept out of harms way.

see also...

- Solid Disk Handwheels SHA
- Countersunk Washers GN 184 (for Axial Fixing)

On request

- Other modifications such as inch and metric bores, keyways, set screw holes, cross holes, etc.

How to order	1 Handwheel diameter d_1
SHA-MRP-160-P6-D	2 Pilot hole d_2
	3 Type