



SS Stainless Steel

**Metric table**

1			2		Dimensions in: millimeters - inches				
$l_1$	GN 99.5	GN 99.6 AISI 304	GN 99.6 AISI 316L	$d_1$ Thread	$d_2$	$d_3$	$h_1$	$h_2 \approx$	$l_2 \approx$
63	63	63	63	M 8	16	10	12.5	30.5	60
2.48	2.48	2.48	2.48		.63	.39	.49	1.20	2.36
80	80	80	80	M 10	20	12	15	37	76
3.15	3.15	3.15	3.15		.79	.47	.59	1.46	2.99
100	100	100	100	M 12	25	14	19	46	95
3.94	3.94	3.94	3.94		.98	.55	.75	1.81	3.74
125	125	-	-	M 16	32	18	25	58.5	119
4.92	4.92	-	-		1.26	.71	.98	2.30	4.69
160	160	-	-	M 20	40	20	31	73	152
6.30	6.30	-	-		1.57	.79	1.22	2.87	5.98

**Specification**

- GN 99.5**  
Steel, zinc plated, blue passivated finish
- GN 99.6**  
Stainless steel, matte shot-blasted finish  
- European Standard No. 1.4301 (AISI 304)  
- European Standard No. 1.4404 (AISI 316L) **A4**
- Clamp arm  
Butt-welded to tapped hub
- RoHS compliant

**On request**

- Special inch and metric bores or threads

**Information**

Latest production techniques make these GN 99.5 and GN 99.6 clamp nuts an extremely good value.

see also...

- Clamping Levers DIN 99 (Steel, Blackened Finish)
- Clamping Levers DIN 99 (Stainless Steel, Matte Shot-Blasted Finish)
- Clamp Nuts GN 206 (Malleable Iron)
- Clamp Nuts GN 206 (Stainless Steel)

How to order (Steel)	1 Lever length $l_1$
<b>GN 99.5-100-M12</b>	2 Thread $d_1$
How to order (Stainless steel AISI 304)	1 Lever length $l_1$
<b>GN 99.6-80-M10</b>	2 Thread $d_1$
How to order (Stainless steel AISI 316L)	1 Lever length $l_1$
<b>GN 99.6-80-M10-A4</b>	2 Thread $d_1$
	3 Material