



3 Type

- A Without handle
- D With revolving handle

Universal table

Dimensions in: millimeters - inches

1 d_1	2 Pilot hole d_2	d_3	d_4	d_6	b	s	$l_{1-0.5}$	$l_{2-0.5}$	$l_3 \approx$	l_4	l_5	d_5 Thread
100 3.94	P 4	24 .94	21 .83	18 .71	20 .79	15 .59	24 .94	12 .47	46 1.81	50 1.97	96 3.78	M 6
125 4.92	P 6	24 .94	21 .83	20 .79	24 .94	17 .67	28 1.10	12 .47	51 2.01	50 1.97	101 3.98	M 6
160 6.30	P 6	32 1.26	23 .91	30 1.18	28 1.10	20 .79	31 1.22	15 .59	61 2.40	70 2.76	131 5.16	M 8
200 7.87	P 6	40 1.57	26 1.02	35 1.38	32 1.26	24 .94	40 1.57	15 .59	74 2.91	90 3.54	164 6.46	M 10

Specification

- Nylon plastic
 - Glass filled
 - Temperature resistant up to 230 °F (110 °C)
 - Black, matte finish
- Hub bushing
 - Steel, zinc plated, molded-in
- Revolving handles
 - Nylon plastic
 - Glass filled
 - Black, matte finish
 - Spindle
 - Steel, zinc plated
- RoHS compliant

Information

V3RA nylon plastic handwheels are of modern design. They are an excellent choice for light to medium duty applications.

No mounting hole in rim for handwheel without handle. Handle shipped loose; mounting of handle is required.

see also...

- Three Spoked Handwheels V3RA-MRE
- Countersunk Washers GN 184 (for Axial Fixing)

On request

- Other modifications such as inch and metric bores, keyways, set screw holes, etc.

How to order V3RA-160-P6-D	1	Handwheel diameter d_1
	2	Pilot hole d_2
	3	Type

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4