




Universal table

1	2	Dimensions in: millimeters / inches										
d ₁	d ₂ Pilot hole	d ₃	d ₄	b	s	l ₁ − 0.5	l ₂ − 0.5	l ₃ ≈	l ₄	l ₅	l ₆	d ₅
100 3.94	P 4	24 0.94	21 0.83	20 0.79	15 0.59	24 0.94	12 0.47	46 1.81	54 2.13	100 3.94	50 1.97	M 4
125 4.92	P 6	24 0.94	21 0.83	24 0.94	17 0.67	28 1.10	12 0.47	51 2.01	54 2.13	105 4.13	54 2.13	M 4
160 6.30	P 6	32 1.26	23 0.91	28 1.10	20 0.79	31 1.22	15 0.59	61 2.40	74 2.91	135 5.31	65 2.56	M 5
200 7.87	P 6	40 1.57	26 1.02	32 1.26	21 0.83	40 1.57	15 0.59	74 2.91	94 3.70	168 6.61	79 3.11	M 6

Specification

Body

- Nylon plastic
- Glass filled
 - Operating temperature up to 230 °F (110 °C)
 - Black, matte finish

Hub bushing

Steel, zinc plated

Retractable handle PGR

- Nylon plastic
- Glass filled
 - Black, matte finish
 - Retractable mechanism / spindle
 - Chrome plated steel hub
 - Zinc plated steel stem

RoHS

On request

- Other modifications such as inch and metric bores, keyways, set screw holes, cross holes, etc.

Nylon plastic three spoked handwheels V3RA-MRE with revolving retractable handle are distinguished by their modern design. By pulling up on the handle 90°, the handle locks into the rotating position. Disengage the handle by pulling it out and moving it down 90° back to the center of the handwheel. A compression spring secures the handle in either position.

These handwheels are an excellent choice for applications requiring the handle to be kept out of harms way.

see also...	Page
V3RA Three Spoked Handwheels	QVX

Technical Information

Keyways WN 6885 / DIN 6885-1	QVX
Plastic Characteristics	QVX

Accessory

GN 184 Countersunk Washers (for Axial Fixing)	QVX
---	-----

How to order	1 Handwheel diameter d_1
V3RA-MRE-160-P6-D	2 Pilot hole d_2
	3 Type