



ELESA original design VR.FP / VR.FP +I

2 Bore Code
BLANK Without bore

3 Type
A Without handle
D With revolving handle

Universal table

Dimensions in: inches - millimeters

1 d ₁	2 Bore	d ₂	d ₃	b	l ₁	l ₂	l ₃	l ₄	l ₅	d ₄	d ₅
3.94 100	Blank	.94 24	.79 20	.55 14	1.42 36	.47 12	1.57 40	1.57 40	1.46 37	.71 18	M 6
4.92 125	Blank	.94 24	.79 20	.71 18	1.42 36	.47 12	1.77 45	1.97 50	1.85 47	.83 21	M 8
6.30 160	Blank	1.26 32	.94 24	.87 22	1.50 38	.59 15	1.97 50	2.56 65	2.32 59	.91 23	M 8
7.09 180	Blank	1.57 40	1.22 31	.94 24	1.69 43	.59 15	2.20 56	3.15 80	2.68 68	1.02 26	M 10
7.87 200	Blank	1.57 40	1.22 31	.94 24	1.69 43	.59 15	2.20 56	3.15 80	2.99 76	1.02 26	M 10
9.84 250	Blank	1.93 49	1.50 38	1.18 30	1.73 44	.59 15	2.60 66	3.54 90	3.86 98	1.10 28	M 10
11.42 290	Blank	2.28 58	1.85 47	1.26 32	2.20 56	.71 18	3.07 78	3.94 100	4.45 113	1.22 31	M 12
14.76 375	Blank	2.28 58	2.28 58	1.57 40	3.03 77	1.02 26	4.25 108	3.94 100	6.30 160	1.22 31	M 14

Specification

- Plastic
Duroplast (Phenolic PF)
- High strength reinforced
- Black, glossy finish
- Hub bushing
Steel, blackened finish, molded-in
- Revolving handles
- Plastic, Duroplast
Black, glossy finish
- Threaded spindle
Steel, zinc plated
- RoHS compliant

On request

- Other modifications such as inch and metric bores, keyways, set screw holes, etc.

Information

EN 950 three spoked handwheels are resistant to solvents, oils, grease and other chemical agents.

see also...

- Countersunk Washers GN 184 (for Axial Fixing)

How to order	1 Handwheel diameter d ₁
1	2 Bore code
2	3 Type

EN 950-180-BLANK-D

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

