



**3 Type**

- A Without handle
- D With revolving handle

**Universal table**

Dimensions in: millimeters - inches

<b>1</b> $d_1$	<b>2</b> $d_2$ Pilot hole	$b$	$d_3$	$d_4$	$d_5$ Thread	$d_6$	$l_1$	$l_2 \approx$	$l_3 \approx$	$l_4$	$l_5$	$r$	$s$
50 1.97	P 4	11 0.43	16 0.63	13 0.51	M 6	13.5 0.53	20 0.79	9 0.35	23 0.91	27 1.06	50 1.97	20 0.79	10 0.39
65 2.56	P 4	13 0.51	20 0.79	13 0.51	M 6	15.5 0.61	24 0.94	10 0.39	28 1.10	27 1.06	55 2.17	26 1.02	13 0.51
80 3.15	P 4	14 0.55	20 0.79	17 0.67	M 6	15.5 0.61	27 1.06	10 0.39	31 1.22	40 1.57	71 2.80	32.5 1.28	15 0.59
100 3.94	P 4	14 0.55	24 0.94	21 0.83	M 8	20 0.79	29 1.14	11 0.43	35 1.38	50 1.97	85 3.35	42 1.65	16 0.63
125 4.92	P 6	16 0.63	32 1.26	23 0.91	M 8	24 0.94	35 1.38	13 0.51	44 1.73	55 2.17	99 3.90	53.5 2.11	18 0.71
150 5.91	P 6	18 0.71	32 1.26	25 0.98	M 10	28 1.10	37 1.46	13 0.51	48 1.89	65 2.56	113 4.45	65 2.56	20 0.79
200 7.87	P 6	21 0.83	40 1.57	28 1.10	M 10	34 1.34	44 1.73	16 0.63	58 2.28	85 3.35	143 5.63	88 3.46	24 0.94
250 9.84	P 6	22 0.87	48 1.89	28 1.10	M 10	40 1.57	49 1.93	17 0.67	66 2.60	85 3.35	151 5.94	110 4.33	30 1.18
300 11.81	P 6	24 0.94	58 2.28	28 1.10	M 10	56.5 2.22	55 2.17	18 0.71	76 2.99	85 3.35	161 6.34	132.5 5.22	35 1.38

**Specification**

- Plastic  
Duroplast (Phenolic PF)  
- Temperature resistant up to 300 °F (150 °C)  
- Black
- Hub bushing  
Steel, zinc plated
- Revolving handle  
Plastic  
Duroplast (Phenolic PF)  
- Black, shiny finish  
- Threaded spindle  
Steel, zinc plated
- *Plastic Characteristics* → page 2135
- **RoHS compliant**

**Information**

VPRA solid disk handwheels with revolving handle are distinguished by their modern design. An excellent choice for light-medium duty applications.

No mounting hole in rim for handwheel without handle. Handle shipped loose; mounting of handle is required.

see also...

- *Three Spoked Handwheels VRAF-MR* → page 263
- *Countersunk Washers GN 184 (for Axial Fixing)* → page 1150

**On request**

- Other modifications such as inch and metric bores, keyways, set screw holes, etc.

**How to order**

**VPRA-50-P4-A**

<b>1</b>	Handwheel diameter $d_1$
<b>2</b>	Pilot hole $d_2$
<b>3</b>	Type