



ELESA original design VR.FP / VR.FP I

2 Bore Code
BLANK Without Bore

3 Type
A Without handle
D With revolving handle

Universal table

Dimensions in: inches - millimeters

1 d ₁	2 Bore	d ₂	d ₃	b	l ₁	l ₂	l ₃	l ₄	l ₅	d ₄	d ₅
3.94 100	Blank	.94 24	.79 20	.55 14	1.42 36	.47 12	1.57 40	1.57 40	1.46 37	.71 18	M 6
4.92 125	Blank	.94 24	.79 20	.71 18	1.42 36	.47 12	1.77 45	1.97 50	1.85 47	.83 21	M 8
6.30 160	Blank	1.26 32	.94 24	.87 22	1.50 38	.59 15	1.97 50	2.56 65	2.32 59	.91 23	M 8
7.09 180	Blank	1.57 40	1.22 31	.94 24	1.69 43	.59 15	2.20 56	3.15 80	2.68 68	1.02 26	M 10
7.87 200	Blank	1.57 40	1.22 31	.94 24	1.69 43	.59 15	2.20 56	3.15 80	2.99 76	1.02 26	M 10
9.84 250	Blank	1.93 49	1.50 38	1.18 30	1.73 44	.59 15	2.60 66	3.54 90	3.86 98	1.10 28	M 10
11.42 290	Blank	2.28 58	1.85 47	1.26 32	2.20 56	.71 18	3.07 78	3.94 100	4.45 113	1.22 31	M 12
14.76 375	Blank	2.28 58	2.28 58	1.57 40	3.03 77	1.02 26	4.25 108	3.94 100	6.30 160	1.22 31	M 14

Specification

- Plastic
 Duroplast (Phenolic PF)
 - High strength reinforced
 - Black, glossy finish
- Hub bushing
 Steel, black oxid finish, molded-in
- Revolving handles
 - Plastic, Duroplast (Phenolic PF)
 Black, glossy finish
 - Threaded spindle
 Steel, zinc plated
- Both dimensions, inch and metric, are interchangeable
- RoHS compliant

On request

- Other modifications such as inch and metric bores, keyways, set screw holes, etc.

Information

EN 950 three spoked handwheels are resistant to solvents, oils, grease and other chemical agents.

How to order	1 Handwheel diameter d ₁
1 2 3 EN 950-180-BLANK-D	2 Bore code
	3 Type