



Metric table

Dimensions in: millimeters - inches

d ₁	d ₂			d ₃	b	h ₁	h ₂	h ₃	t		
	Thread	GB	GB-FP						GB	GB-FP	
34 1.34	M 6	M 8	M 6	-	7 .28	14 .55	18 .71	4 .16	.3 .01	9 .35	15 .59
47 1.85	M 6	M 8	M 6	M 8	9 .35	17 .67	20 .79	4 .16	.3 .01	13 .51	15 .59

Specification

- Wing body
Nylon plastic
- Glass filled
- Temperature resistant up to 230 °F (110 °C)
- Black, matte finish
- Tapped insert
Brass, molded-in
- RoHS compliant

On request

- For certain minimum quantities, custom colors or special studs

Information

GB and GB-FP wing nuts offer an extended hub for better surface contact and a comfortable grip for quick two finger clamping applications.

The tapped through type allows full clamping, unrestricted the threaded stud the wing nut is being used on.

see also...

- Wing Screws GP (with Steel Threaded Stud)

How to order (Blind tapped insert) 1 2 GB-34-M6	1	Handle diameter d ₁
	2	Thread d ₂
How to order (Through tapped insert) 1 2 GB-FP-47-M8	1	Handle diameter d ₁
	2	Thread d ₂