




Universal table

1 d₁	2 d₂ Pilot hole	d ₃	d ₄	b	l ₁	l ₂	l ₃	l ₄	l ₅	d ₅
100 3.94	P 4	24 0.94	17 0.67	15 0.59	33 1.30	11 0.43	40 1.57	45 1.77	85 3.35	M 8
125 4.92	P 6	24 0.94	23 0.91	17 0.67	36 1.42	13 0.51	46 1.81	61 2.40	107 4.21	M 8
150 5.91	P 6	32 1.26	25 0.98	20 0.79	37 1.46	13 0.51	49 1.93	71 2.80	120 4.72	M 10
175 6.89	P 6	40 1.57	25 0.98	22 0.87	41 1.61	16 0.63	56 2.20	71 2.80	127 5.00	M 10
200 7.87	P 6	40 1.57	28 1.10	24 0.94	44 1.73	16 0.63	61 2.40	92 3.62	153 6.02	M 10
250 9.84	P 6	48 1.89	28 1.10	28 1.10	49 1.93	17 0.67	72 2.83	92 3.62	164 6.46	M 10
300 11.81	P 6	58 2.28	28 1.10	34 1.34	54 2.13	18 0.71	78 3.07	92 3.62	170 6.69	M 10

Specification

Body

- Plastic, Phenolic (PF)
- Fiber reinforced
 - Operating temperature up to 302 °F (150 °C)
 - Black, shiny finish

Hub bushing

Steel, zinc plated

Revolving handle

- Plastic, Phenolic (PF)
- Black, shiny finish
 - Rim
 - Steel, zinc plated

RoHS

On request

- Other modifications such as inch and metric bores, keyways, set screw holes, etc.

Three spoked handwheels VRAF are distinguished by modern design. An excellent choice for light-medium duty applications. No mounting hole in rim for handwheel without handle. Handle shipped loose; mounting of handle is required.

see also...	Page
VRAF-MR Three Spoked Handwheels	QVX

Technical Information

Keyways WN 6885 / DIN 6885-1	QVX
Plastic Characteristics	QVX

Accessory

GN 184 Countersunk Washers (for Axial Fixing)	QVX
---	-----