



**Metric table**



Dimensions in: millimeters - inches

Size	d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	b	h	t	Part number bearing lock washer 	Part number hook spanner wrench 
0	M 10 x 0.75	18 <i>0.71</i>	13.5 <i>0.53</i>	3 <i>0.12</i>	4 <i>0.16</i>	2 <i>0.08</i>	MB-0	DIN 1810-A16-20
1	M 12 x 1	22 <i>0.87</i>	17 <i>0.67</i>	3 <i>0.12</i>	4 <i>0.16</i>	2 <i>0.08</i>	MB-1	DIN 1810-A16-20
2	M 15 x 1	25 <i>0.98</i>	21 <i>0.83</i>	4 <i>0.16</i>	5 <i>0.20</i>	2 <i>0.08</i>	MB-2	DIN 1810-A25-28
3	M 17 x 1	28 <i>1.10</i>	24 <i>0.94</i>	4 <i>0.16</i>	5 <i>0.20</i>	2 <i>0.08</i>	MB-3	DIN 1810-A25-28
4	M 20 x 1	32 <i>1.26</i>	26 <i>1.02</i>	4 <i>0.16</i>	6 <i>0.24</i>	2 <i>0.08</i>	MB-4	DIN 1810-A30-32
5	M 25 x 1.5	38 <i>1.50</i>	32 <i>1.26</i>	5 <i>0.20</i>	7 <i>0.28</i>	2 <i>0.08</i>	MB-5	DIN 1810-A34-36
6	M 30 x 1.5	45 <i>1.77</i>	38 <i>1.50</i>	5 <i>0.20</i>	7 <i>0.28</i>	2 <i>0.08</i>	MB-6	DIN 1810-A45-50
7	M 35 x 1.5	52 <i>2.05</i>	44 <i>1.73</i>	5 <i>0.20</i>	8 <i>0.31</i>	2 <i>0.08</i>	MB-7	DIN 1810-A52-55
8	M 40 x 1.5	58 <i>2.28</i>	50 <i>1.97</i>	6 <i>0.24</i>	9 <i>0.35</i>	2.5 <i>0.10</i>	MB-8	DIN 1810-A58-62
9	M 45 x 1.5	65 <i>2.56</i>	56 <i>2.20</i>	6 <i>0.24</i>	10 <i>0.39</i>	2.5 <i>0.10</i>	MB-9	DIN 1810-A65-70
10	M 50 x 1.5	70 <i>2.76</i>	61 <i>2.40</i>	6 <i>0.24</i>	11 <i>0.43</i>	2.5 <i>0.10</i>	MB-10	DIN 1810-A68-75

**Specification**

- Low carbon steel, plain finish
- RoHS compliant

**Accessory**

- Bearing lock washers MB (Part number, see table)
- Hook spanner wrenches DIN 1810 (Part number, see table)

**On request**

- Additional sizes

**Information**

KM bearing lock nuts according to DIN 981 are mainly utilized to secure bearings onto a shaft.

<p>How to order</p> <p><b>KM-0</b></p>	<p>1 Size</p>
--	---------------