


Specification



- Lever body
Plastic **KT**
Nylon thermoplastic
- Glass fiber reinforced
- With molded-in stainless steel inlay
- Temperature resistant up to 230 °F (110 °C)
- Color
Black, RAL 9005, textured finish **SW**
Orange, RAL 2004, textured finish **OS**
Gray, RAL 7035, textured finish **GS**
- Insert / retaining screw
Steel, zinc plated, blue passivated finish
- Plastic Characteristics → page 2135
- RoHS compliant

On request

- Special colors and threads

Information

Made in the USA, WN 300.2 adjustable levers are the result of modern industrial design: glass fiber reinforced thermoplastic with molded-in stainless steel inlay.

All such levers have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

see also...

- Adjustable Levers WN 300.2 (Nylon Plastic, with Zinc Plated Steel Threaded Stud) → page 422
- Adjustable Levers GN 300.2 (Zinc Die-Cast, with Zinc Plated Steel Insert) → page 404
- Adjustable Levers WN 300 (Nylon Plastic, with Blackened Steel Insert) → page 420
- Adjustable Levers GN 300 (Zinc Die-Cast, with Blackened Steel Insert) → page 402
- Adjustable Levers WN 303 (Nylon Plastic, with Push Button) → page 444
- Adjustable Levers GN 303 (Zinc Die-Cast, with Push Button) → page 436

How to order (Inch)	1 Material
WN300.2-KT-78-3/8X16-OS	2 Lever length l ₁
	3 Thread d ₁
	4 Color

How to order (Metric)	1 Material
WN300.2-KT-92-M10-GS	2 Lever length l ₁
	3 Thread d ₁
	4 Color

Inch table

2

3

Dimensions in: inches - *millimeters*

l₁	d₁			d₃	d₄	h₁	h₂	h₃	h₄ Stroke	t min.
1.77 45	10 x 32	10 x 24	1/4 x 20	0.39 10	0.57 14.5	0.96 24.5	0.16 4	1.38 35	0.14 3.5	0.35 9
2.48 63	1/4 x 20	5/16 x 18	-	0.53 13.5	0.76 19.4	1.22 31	0.26 6.5	1.77 45	0.16 4	0.43 11
3.07 78	5/16 x 18	3/8 x 16	-	0.63 16	0.87 22.2	1.42 36	0.31 8	2.17 55	0.16 4	0.55 14
3.62 92	3/8 x 16	1/2 x 13	-	0.75 19	0.99 25.2	1.69 43	0.43 11	2.56 65	0.16 4	0.67 17

Metric table

2

3

Dimensions in: millimeters - *inches*

l₁	d₁			d₃	d₄	h₁	h₂	h₃	h₄ Stroke	t min.
30 1.18	M 4	M 5	M 6	10 0.39	14.5 0.57	24.5 0.96	4 0.16	30.5 1.20	3.5 0.14	9 0.35
45 1.77	M 4	M 5	M 6	10 0.39	14.5 0.57	24.5 0.96	4 0.16	35 1.38	3.5 0.14	9 0.35
63 2.48	M 6	M 8	-	13.5 0.53	19.4 0.76	31 1.22	6.5 0.26	45 1.77	4 0.16	11 0.43
78 3.07	M 8	M 10	-	16 0.63	22.2 0.87	36 1.42	8 0.31	55 2.17	4 0.16	14 0.55
92 3.62	M 10	M 12	-	19 0.75	25.2 0.99	43 1.69	11 0.43	65 2.56	4 0.16	17 0.67

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

