



- 4 Type**
- A Without pad
 - B With light duty pad
 - D With heavy duty pad

Inch table

Dimensions in: inches - millimeters

1			2		3											
d ₁			d ₂ Thread		l ₁		l ₂		l ₃		l ₄ Light duty pad Heavy duty pad		A/F		Max. load Light duty pad Without pad / heavy duty pad	
2.00 50.8	2.50 63.5	-	3/8 x 16	3.00 76.2	4.00 101.6	6.00 152.4	8.00 203.2	0.97 24.6	0.34 8.6	0.42 10.7	0.57 14.5	3/4	1500 lbf 6672.33 N	2000 lbf 8896.44 N		
2.00 50.8	2.50 63.5	-	1/2 x 13	3.00 76.2	4.00 101.6	6.00 152.4	8.00 203.2	0.97 24.6	0.34 8.6	0.42 10.7	0.57 14.5	3/4	3000 lbf 13344.66 N	3500 lbf 15568.77 N		
3.00 76.2	4.00 101.6	-	1/2 x 13	3.00 76.2	4.00 101.6	6.00 152.4	8.00 203.2	1.04 26.4	0.34 8.6	0.42 10.7	0.57 14.5	3/4	3000 lbf 13344.66 N	3500 lbf 15568.77 N		
2.00 50.8	2.50 63.5	-	5/8 x 11	3.00 76.2	4.00 101.6	6.00 152.4	8.00 203.2	0.97 24.6	0.34 8.6	0.42 10.7	0.57 14.5	7/8	4500 lbf 20016.99 N	5000 lbf 22241.10 N		
3.00 76.2	4.00 101.6	6.00 152.4	5/8 x 11	3.00 76.2	4.00 101.6	6.00 152.4	8.00 203.2	1.04 26.4	0.34 8.6	0.42 10.7	0.57 14.5	7/8	4500 lbf 20016.99 N	5000 lbf 22241.10 N		
3.00 76.2	4.00 101.6	6.00 152.4	3/4 x 10	3.00 76.2	4.00 101.6	6.00 152.4	8.00 203.2	1.04 26.4	0.34 8.6	0.42 10.7	0.57 14.5	11/16	5500 lbf 24465.21 N	6000 lbf 26689.32 N		

Specification

- **LP 100**
Base / threaded stud / hexagon nuts
Steel, zinc plated, blue passivated finish
- **LP 100.1**
Base / threaded stud / hexagon nuts
Stainless steel
European Standard No. 1.4305 (AISI 303)
- Vibration damping pad
Rubber, waffle-style
- **RoHS compliant**

On request

- Metric sizes

Information

LP 100 and LP 100.1 anti-vibration leveling mounts are for medium to heavy duty applications. These durable mounts are utilized where a lower base height is required.

A coupling nut is not recommended to use for installation. Use a nut or tapped hole of 1 - 1 1/2 times the thread diameter of the threaded stud.

To insure a proper leveling mount size, divide the machine weight by the number of mounts required. This will equal the pounds or load per mount.

Two hexagon nuts are included with each leveling mount.

see also...

- "Anti-Vibe®" Anti-Vibration Leveling Mounts AVM (Inch Thread, Steel)
- Vibration Damping Leveling Feet GN 342.2 (Metric Thread, Steel)

How to order (Steel)		1	Base diameter d ₁
		2	Thread d ₂
		3	Stud length l ₁
		4	Type
		LP100-2.50-1/2X13-4.00-B	

How to order (Stainless steel)		1	Base diameter d ₁
		2	Thread d ₂
		3	Stud length l ₁
		4	Type
		LP100.1-4.00-5/8X11-3.00-A	