



- 5 Type**
- MS** Brass tip
 - KU** Plastic tip (Polyacetal POM)
 - DZ** Steel, hardened oval tip
 - ZK** Ball end
 - KD** Ball end with swivel thrust pad

Metric table

2		3		4		Dimensions in: millimeters - inches																
l_1	d_1 Thread	l_2		d_3	d_4	d_5	d_6	d_7 +0.05	d_8	h_1	h_2	h_3	h_4 Stroke	l_3	l_4	l_5	l_6	l_7				
30 1.18	M 6	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	10 0.39	14.5 0.57	4 0.16	3.5 0.14	4.5 0.18	15 0.59	24.5 0.96	4 0.16	30.5 1.20	3.5 0.14	1 0.04	1.3 0.05	1.8 0.07	5.1 0.20	3.6 0.14
45 1.77	M 6	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	10 0.39	14.5 0.57	4 0.16	3.5 0.14	4.5 0.18	15 0.59	24.5 0.96	4 0.16	35 1.38	3.5 0.14	1 0.04	1.3 0.05	1.8 0.07	5.1 0.20	3.6 0.14
63 2.48	M 8	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	13.5 0.53	19.4 0.76	6 0.24	5 0.20	6.1 0.24	18 0.71	31 1.22	6.5 0.26	45 1.77	4 0.16	1.5 0.06	1.6 0.06	2.5 0.10	6.2 0.24	4.2 0.17
63 2.48	M 10	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	13.5 0.53	19.4 0.76	8 0.31	6.5 0.26	7.8 0.31	21 0.83	31 1.22	6.5 0.26	45 1.77	4 0.16	2 0.08	1.9 0.07	3.5 0.14	7.3 0.29	4.3 0.17

Specification

- Lever body
Plastic **KT**
Nylon thermoplastic
Temperature resistant up to 230 °F (110 °C)
- Color
Black, RAL 9005, textured finish **● SW**
Orange, RAL 2004, textured finish **● OS**
Gray, RAL 7035, textured finish **● GS**
- Threaded stud / retaining screw
Steel
- Blackened finish
- Property class 5.8
- Thrust pad
Plastic
Technopolymer (Polyacetal POM)
- Temperature resistant up to 176 °F (80 °C)
- Black, matte finish
- RoHS compliant

On request

- Inch threads
- Threaded stud in stainless steel
- Straight lever (WN 302)

Information

WN 306 adjustable levers are the result of modern industrial design: glass fiber reinforced thermoplastic with molded-in stainless steel inlay.

They have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

The brass and plastic tipped studs (types MS / KU) help to avoid damage to the workpiece being clamped.

The hardened tipped stud (type DZ) provides an oval point-shaped pressure point.

The swivel thrust pad (type KD) is easily clipped on and taken off. Thrust pads are supplied unmounted.

see also...

- Adjustable Levers WN 300 (without Special Tipped Threaded Studs)

How to order	
1	Lever body material
2	Lever length l_1
3	Thread d_1
4	Thread length l_2
5	Type
6	Color

WN 306-KT-30-M6-16-DZ-SW