



3 Type

- A Without handle
- D With revolving handle

Universal table

Dimensions in: millimeters - inches

1 d ₁	2 d ₂ Pilot hole	d ₃	d ₄	d ₆	b	s	l _{1-0.5}	l _{2-0.5}	l _{3 ≈}	l ₄	l ₅	d ₅ Thread
100 3.94	P 4	24 .94	21 .83	18 .71	20 .79	15 .59	24 .94	12 .47	46 1.81	50 1.97	96 3.78	M 6
125 4.92	P 6	24 .94	21 .83	20 .79	24 .94	17 .67	28 1.10	12 .47	51 2.01	50 1.97	101 3.98	M 6
160 6.30	P 6	32 1.26	23 .91	30 1.18	28 1.10	20 .79	31 1.22	15 .59	61 2.40	70 2.76	131 5.16	M 8
200 7.87	P 6	40 1.57	26 1.02	35 1.38	32 1.26	24 .94	40 1.57	15 .59	74 2.91	90 3.54	164 6.46	M 10

Specification

- Nylon plastic
 - Glass filled
 - Temperature resistant up to 230 °F (110 °C)
 - Black, matte finish
- Hub bushing
 - Steel, zinc plated, molded-in
- Revolving handles
 - Nylon plastic
 - Glass filled
 - Black, matte finish
 - Spindle
 - Steel, zinc plated
- Both dimensions, inch and metric, are interchangeable
- RoHS compliant

On request

- Other modifications such as inch and metric bores, keyways, set screw holes, etc.

Information

V3RA thermoplastic handwheels are of modern design. They are an excellent choice for light to medium duty applications.

No mounting hole in rim for handwheel without handle. Handle shipped loose; mounting of handle is required.

see also...

- *Three Spoked Handwheels V3RA-MRE*
- *Countersunk Washers GN 184 (for Axial Fixing)*

How to order V3RA-160-P6-D	1	Handwheel diameter d ₁
	2	Pilot hole d ₂
	3	Type

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4