



**Inch table**

Dimensions in: inches - millimeters

<sup>1</sup> d <sub>1</sub> Thread	<sup>2</sup> l <sub>1</sub> Nominal length		d <sub>2</sub>	d <sub>3</sub>	l <sub>2</sub>	l <sub>3</sub>	A/F
10 x 24	0.250 6.4	0.625 15.9	0.125 3.2	0.125 3.2	0.047 1.2	0.047 1.2	0.094
1/4 x 20	0.375 9.5	0.750 19.1	0.125 3.2	0.125 3.2	0.047 1.2	0.063 1.6	0.125
5/16 x 18	0.375 9.5	0.750 19.1	0.188 4.8	0.188 4.8	0.063 1.6	0.094 2.4	0.156
3/8 x 16	0.375 9.5	1.00 25.4	0.188 4.8	0.188 4.8	0.063 1.6	0.094 2.4	0.188
1/2 x 13	0.625 15.9	1.00 25.4	0.313 8.0	0.250 6.4	0.094 2.4	0.125 3.2	0.250

**Specification**

- Body  
Steel
- Property class 5.8
- Blackened finish

- Tip
- Brass
- Plastic (Nylon 66)

**MS  
KU**

- [Strength Values of Screws](#) → page 2127
- [Plastic Characteristics](#) → page 2135

- [RoHS compliant](#)

**Information**

WN 913.3 set screws with brass or plastic tip are used in applications where markings, pressure dents and damage to the workpiece are unacceptable.

These set screws can also be used with a variety of different hand operating components, such as levers, hand knobs, star knobs, and knurled nuts.

see also...

- [Set Screws GN 913.3 \(Metric Size\)](#) → page 1099
- [Set Screws GN 913.2 \(with Hardened Tip\)](#) → page 1101
- [Socket Set Screws GN 605 \(with Flat Ball\)](#) → page 1102
- [Set Screws GN 913.6 \(with Retaining Magnet\)](#) → page 2026

**How to order**

**WN 913.3-1/2X13-0.625-KU**

<sup>1</sup>	Thread d <sub>1</sub>
<sup>2</sup>	Thread length l <sub>1</sub>
<sup>3</sup>	Tip material