



Inch



Inch table

Dimensions in: inches / millimeters

¹ l ₁	² d ₁ Bore	³ h ₂	h ₄	h ₅	h ₁	h ₃	d ₂	l ₂	d ₃ Ø Handle	Handle thread
3.94 100.1	B 3/8	3.40 86.4	2.56 65	7.75 196.9	1.57 39.9	2.10 53.3	0.625 15.9	6.28 159.5	0.98 24.9	M 8

Specification

Crank body

- Nylon plastic
- Glass filled
- Operating temperature up to 230 °F (110 °C)
- Black, matte finish

Hub bushing

Steel, zinc plated

Revolving handle

- Plastic, Phenolic (PF)
- Black, shiny finish
- Threaded spindle
- Steel, zinc plated

Spring loaded retracting mechanism

Steel, zinc plated

RoHS

On request

- For certain minimum quantities, inch bore sizes from .250"-.506" and metric bore sizes from 6 mm-12 mm
- For certain minimum quantities, square mechanisms can also be manufactured

Retracting hand cranks WRHC are just one of many specials that have become a standard product.

Can be used in any application requiring the complete crank handle to be folded out of the way.

Please call us with your application requirements.

see also...

	Page
MV-M Crank Handles	QVX

Technical Information

Keyways WN 6885 / DIN 6885-1	QVX
Plastic Characteristics	QVX

How to order

¹ ² ³
WRHC-3.94-B3/8-3.40

1	Length l ₁
2	Blind bore d ₁
3	Height h ₂