




Specification	1	5
Lever body		
Plastic, Nylon thermoplastic	KT	
• Glass fiber reinforced		
• With molded-in stainless steel inlay		
• Operating temperature up to 230 °F (110 °C)		
• Color		
- Black, RAL 9005, textured finish	● SW	
- Orange, RAL 2004, textured finish	● OS	
- Gray, RAL 7035, textured finish	● GS	
Threaded stud / Retaining screw		
Steel, zinc plated, blue passivated finish		
RoHS		
On request		
• Special colors and threads		

Made in the USA, adjustable levers WN 300.2 are the result of modern industrial design: glass fiber reinforced thermoplastic with molded-in stainless steel inlay.

All such levers have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

see also...	Page
WN 300.2 Adjustable Levers (Nylon Plastic, with Zinc Plated Steel Insert)	QVX
GN 300.2 Adjustable Levers (Zinc Die-Cast, with Zinc Plated Steel Threaded Stud)	QVX
WN 300 Adjustable Levers (Nylon Plastic, with Blackened Steel Threaded Stud)	QVX
GN 300 Adjustable Levers (Zinc Die-Cast, with Blackened Steel Threaded Stud)	QVX
WN 303 Adjustable Levers (Nylon Plastic, with Push Button)	QVX
GN 303 Adjustable Levers (Zinc Die-Cast, with Push Button)	QVX

Technical Information	
Plastic Characteristics	QVX

Inch table

2**3****4**

Dimensions in: inches / millimeters

l₁	d₁	l₂									d₃	d₄	h₁	h₂	h₃	h₄ Stroke
1.77 45	10 x 32	0.39 10	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	-	-	-	0.39 10	0.57 14.5	0.96 24.5	0.16 4	1.38 35	0.14 3.5
1.77 45	10 x 24	0.63 16	0.79 20	1.26 32	-	-	-	-	-	-	0.39 10	0.57 14.5	0.96 24.5	0.16 4	1.38 35	0.14 3.5
1.77 45	1/4 x 20	0.39 10	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	-	0.39 10	0.57 14.5	0.96 24.5	0.16 4	1.38 35	0.14 3.5
2.48 63	1/4 x 20	0.63 16	0.79 20	0.98 25	-	-	-	-	-	-	0.53 13.5	0.76 19.4	1.22 31	0.26 6.5	1.77 45	0.16 4
2.48 63	5/16 x 18	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	0.53 13.5	0.76 19.4	1.22 31	0.26 6.5	1.77 45	0.16 4
2.48 63	3/8 x 16	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	-	0.53 13.5	0.76 19.4	1.22 31	0.26 6.5	1.77 45	0.16 4
3.07 78	3/8 x 16	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	-	0.63 16	0.87 22.2	1.42 36	0.31 8	2.17 55	0.16 4
3.07 78	1/2 x 13	1.26 32	1.57 40	-	-	-	-	-	-	-	0.63 16	0.87 22.2	1.42 36	0.31 8	2.17 55	0.16 4
3.62 92	3/8 x 16	0.98 25	1.26 32	1.38 35	1.57 40	1.77 45	1.97 50	2.48 63	-	-	0.75 19	0.99 25.2	1.69 43	0.43 11	2.56 65	0.16 4
3.62 92	1/2 x 13	0.98 25	1.26 32	1.38 35	1.57 40	1.77 45	1.97 50	2.48 63	-	-	0.75 19	0.99 25.2	1.69 43	0.43 11	2.56 65	0.16 4

Metric table

2**3****4**

Dimensions in: millimeters / inches

l ₁	d ₁		l ₂								d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke
30 1.18	M 4	-	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	-	-	10 0.39	14.5 0.57	24.5 0.96	4 0.16	30.5 1.20	3.5 0.14	
30 1.18	M 5	-	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	10 0.39	14.5 0.57	24.5 0.96	4 0.16	30.5 1.20	3.5 0.14	
30 1.18	M 6	-	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	10 0.39	14.5 0.57	24.5 0.96	4 0.16	30.5 1.20	3.5 0.14	
45 1.77	M 4	-	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	-	-	10 0.39	14.5 0.57	24.5 0.96	4 0.16	35 1.38	3.5 0.14	
45 1.77	M 5	-	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	10 0.39	14.5 0.57	24.5 0.96	4 0.16	35 1.38	3.5 0.14	
45 1.77	M 6	-	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	10 0.39	14.5 0.57	24.5 0.96	4 0.16	35 1.38	3.5 0.14	
63 2.48	M 6	-	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	13.5 0.53	19.4 0.76	31 1.22	6.5 0.26	45 1.77	4 0.16	
63 2.48	M 8	-	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	13.5 0.53	19.4 0.76	31 1.22	6.5 0.26	45 1.77	4 0.16	
78 3.07	M 8	M 10	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	16 0.63	22.2 0.87	36 1.42	8 0.31	55 2.17	4 0.16	
92 3.62	M 10	M 12	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	19 0.75	25.2 0.99	43 1.69	11 0.43	65 2.56	4 0.16	