

Clamp mountings

Range













With clamp mountings, tubes and rods can be fixed with better clamping pressure with minimum space requirement. Standardized hole spacings and thread dimensions make the replacement of mounting clamps very simple and efficient during assembly, thanks to the standardized tool.

The large range of clamp mountings enables almost all positioning options. In particular, swivel clamp mountings can be combined to jointed clamp mountings.

The aluminum-alloy used for the clamp mountings has excellent strength and good chemical resistance. The version with a black anodized surface is additionally protected against corrosion. Together with fastening and clamping screws made from corrosion resistant A2 stainless steel use under unfavorable ambient conditions is possible.

Accessories such as sensor plates, retaining rods and tubes as well as clamping kits complete the range. If required, a suitable retaining magnet (GN 51.6) is available to facilitate rapid repositioning.

Positioning of sensors, scanners, reflectors, cameras, coolant pipes and air nozzles is a typical practical application.

<p>Base plate clamp mountings GN 473</p>		<p>Clamp mountings GN 477</p>	
<p>Two-way clamp mountings GN 474</p>		<p>Twistable two-way clamp mountings GN 475</p>	
<p>T-Clamp mountings GN 476</p>		<p>Attachment clamp mountings GN 478</p>	
<p>Flanged bolts GN 480</p>		<p>Twistable two-way clamp mountings GN 490</p>	
<p>Swivel clamp connector bases GN 485</p>		<p>Swivel clamp mountings GN 482</p>	
<p>T-Swivel clamp mountings GN 483</p>		<p>Attachment clamp mountings GN 484</p>	
<p>Sensor holders GN 479 → Retaining plates GN 479.1</p>		<p>Retaining rods Retaining tubes GN 480.1</p>	