



Specification



- Lever body
Zinc die-cast
- Powder coated
Black, RAL 9005, textured finish **● SW**
Orange, RAL 2004, textured finish **● OS**
- Threaded stud / retaining screw
Stainless steel AISI 303
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

On request

- Special colors, stud lengths, and threads

Information

GN 101.1 adjustable levers have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

see also...

- *Adjustable Levers GN 101 (Steel Threaded Stud)* → page 482
- *Adjustable Levers GN 300.1 (Stainless Steel Threaded Stud)* → page 412
- *Adjustable Levers GN 300.2 (Zinc Plated Steel Threaded Stud)* → page 410
- *Straight Adjustable Levers GN 302.1 (Stainless Steel Threaded Stud)* → page 456
- *Adjustable Levers GN 300.5 (Stainless Steel)* → page 432
- *Adjustable Levers EN 604.1 (Plastic Lever Body)* → page 498

How to order (Inch)	1 Diameter d ₁
GN 101.1-14-10X32-12-SW	2 Thread d ₂
	3 Thread length l ₁
	4 Color
How to order (Metric)	1 Diameter d ₁
GN 101.1-25-M12-40-OS	2 Thread d ₂
	3 Thread length l ₁
	4 Color

Inch table

Dimensions in: inches - millimeters

¹ d ₁	² d ₂	³ l ₁								d ₃	h ₁	h ₂	h ₃	h ₄ Stroke	l ₂
0.55 14	10 x 32	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	-	-	-	0.39 10	0.98 25	0.18 4.5	1.38 35	0.14 3.5	1.77 45
0.55 14	1/4 x 20	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	-	0.39 10	0.98 25	0.18 4.5	1.38 35	0.14 3.5	1.77 45
0.71 18	5/16 x 18	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	0.53 13.5	1.22 31	0.26 6.5	1.77 45	0.16 4	2.44 62
0.71 18	3/8 x 16	0.79 20	0.98 25	1.26 32	1.57 40	-	-	-	-	0.53 13.5	1.22 31	0.26 6.5	1.77 45	0.16 4	2.44 62
0.87 22	3/8 x 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	-	0.63 16	1.42 36	0.31 8	2.05 52	0.16 4	2.91 74
0.87 22	1/2 x 13	0.79 20	0.98 25	1.26 32	-	-	-	-	-	0.63 16	1.42 36	0.31 8	2.05 52	0.16 4	2.91 74
0.98 25	1/2 x 13	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	-	-	0.75 19	1.69 43	0.43 11	2.48 63	0.16 4	3.50 89

Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂	³ l ₁								d ₃	h ₁	h ₂	h ₃	h ₄ Stroke	l ₂
14 0.55	M 5	M 6	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	10 0.39	25 0.98	4.5 0.18	35 1.38	3.5 0.14	45 1.77
18 0.71	M 6	M 8	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	13.5 0.53	31 1.22	6.5 0.26	45 1.77	4 0.16	62 2.44
22 0.87	M 10	-	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	16 0.63	36 1.42	8 0.31	52 2.05	4 0.16	74 2.91
25 0.98	M 12	-	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	-	19 0.75	43 1.69	11 0.43	63 2.48	4 0.16	89 3.50
30 1.18	M 16	-	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	-	-	23 0.91	50.5 1.99	12 0.47	76 2.99	5 0.20	108 4.25

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

