


Cam Action Indexing Plunger / Spring Latch Types

Unlocking by Turning the Plunger Pin over Curves

GN 612 GN 612 ... NI

Lock-out
Pin Ø 4 / 5 / 6 / 8 / 10 / 12 mm
Inch / Metric thread




Features:

- Body in blackened steel or stainless steel
- Plunger pin in nitrided steel or stainless steel
- Lever arm in blackened steel or stainless steel
- Lever arm with or without plastic sleeve
- High precision plunger pin body

GN 612.8

Lock-out
Pin Ø 4 / 5 / 6 / 8 / 10 / 12 mm
Metric thread




Features:

- Body in zinc die-cast with ZNDG Pass Nano® coating
- Plunger pin in zinc plated steel
- Lever arm in plastic
- Reasonably priced version

EN 672 ... ST EN 672 ... NI

Lock-out
Pin Ø 6 / 8 mm
Metric thread




Features:

- Body in plastic
- Plunger pin in hardened steel or stainless steel
- Lever arm in plastic
- Reasonably priced corrosion-resistant version

GN 712

Plunger pin in normal position protruded
Pin Ø 6 / 8 / 10 mm
Metric thread




Features:

- Plunger pin secured, not secured or secured and additionally locked (safety version) in end positions
- Body in zinc plated steel
- Plunger pin in stainless steel
- Lever arm in plastic


GN 712.1

Plunger pin in normal position retracted
Pin Ø 6 / 8 mm
Metric thread



GN 721 GN 721.5

Non lock-out
Pin Ø 5 / 6 / 8 / 10 mm
Metric thread



Features:


- Body in blackened steel or stainless steel
- Plunger pin in nitrided steel or stainless steel
- Lever arm in blackened steel or stainless steel
- Lever arm with or without plastic sleeve
- Right or left hand limit stop
- High precision plunger pin body

Cam Action Indexing Plunger / Spring Latch Types

Unlocking by Turning the Plunger Pin over Curves

GN 721.1
GN 721.6

Lock-out
Pin Ø 5 / 6 / 8 / 10 mm
Metric thread




Features:

- Body in blackened steel or stainless steel
- Plunger pin in nitrided steel or stainless steel
- Lever arm in blackened steel or stainless steel
- Lever arm with or without plastic sleeve
- Right or left hand limit stop
- High precision plunger pin body

GN 612.2

Lock-out
Pin Ø 6 / 8 / 10 / 12 mm




Features:

- Body in blackened steel
- Plunger pin in nitrided steel
- Lever arm in blackened steel
- Lever arm with or without plastic sleeve

GN 612.9

Lock-out
Pin Ø 6 / 8 / 10 / 12 mm




Features:

- Body in black powder coated zinc die-cast
- Plunger pin in zinc plated steel
- Lever arm in plastic
- Reasonably priced version

GN 722.3
GN 722.3 ... A4

Lock-out
Pin Ø 8 / 10 / 12 / 14 mm




Features:

- Body in steel precision casting (zinc plated or black powder coated) or stainless steel precision casting
- Latch pin in zinc plated steel or stainless steel
- Lever arm in zinc plated steel precision casting or stainless steel precision casting
- Left or right indexing cam
- Designed for less precise positioning

GN 722.2
GN 722.2 ... A4

Lock-out
Pin Ø 8 / 10 / 12 / 14 mm




Features:

- Body in steel precision casting (zinc plated or black powder coated) or stainless steel precision casting
- Latch pin in zinc plated steel or stainless steel
- Lever arm in zinc plated steel precision casting or stainless steel precision casting
- Latch position right-angled or parallel to mounting holes
- Designed for less precise positioning

GN 612.10

Lock-out
Pin Ø 6 / 8 / 10 / 12 mm



Features:

- Body in black powder coated zinc die-cast
- Plunger pin in zinc plated steel
- Lever arm in plastic
- Reasonably priced version




Cam Action Indexing Plunger / Spring Latch Types

Unlocking by Turning the Plunger Pin over Curves

GN 612.3
GN 612.3 ... NI

Lock-out
Pin Ø 6 / 8 / 10 / 12 mm

SS Stainless Steel




Features:

- Weldable cam action indexing plunger
- Body in blackened steel or stainless steel
- Plunger pin in nitrided steel or stainless steel
- Lever arm with or without plastic sleeve

GN 722.1 ... ST
GN 722.1 ... A4

Lock-out
Pin Ø 8 / 10 / 12 / 14 mm

SS Stainless Steel



Features:

- Weldable cam action indexing plunger
- Body in blackened steel precision casting or stainless steel precision casting
- Latch pin in zinc plated steel or stainless steel
- Lever arm in zinc plated steel precision casting or stainless steel precision casting
- Designed for less precise positioning