



SS Stainless Steel

2 Type

S Safety lanyard ring

Metric table



Dimensions in: millimeters - inches

d₀ Hub Ø	d₁ +0.5	d₂	d₃ ±0.1	b +0.2	l₁ ≈	l₂ ±0.5	l₃ +0.3
12 0.47	11.4 0.45	1.1 0.04	9.1 0.36	1.7 0.07	18.7 0.74	5 0.20	2.5 0.10
14 0.55	13.2 0.52	1.1 0.04	10.9 0.43	1.8 0.07	19.8 0.78	5 0.20	3.2 0.13
15 0.59	14.6 0.57	1.3 0.05	11.9 0.47	1.8 0.07	22.7 0.89	5.5 0.22	3.2 0.13
16 0.63	15.6 0.61	1.3 0.05	12.9 0.51	1.8 0.07	23.3 0.92	5.5 0.22	3.2 0.13
17 0.67	16.4 0.65	1.3 0.05	13.7 0.54	1.9 0.07	23.8 0.94	5.5 0.22	3.9 0.15
18 0.71	17.6 0.69	1.4 0.06	14.7 0.58	1.9 0.07	26.5 1.04	6 0.24	3.9 0.15
19 0.75	18.6 0.73	1.4 0.06	15.7 0.62	1.9 0.07	27.1 1.07	6 0.24	3.9 0.15
20 0.79	19.6 0.77	1.4 0.06	16.7 0.66	1.9 0.07	27.7 1.09	6 0.24	3.9 0.15
21 0.83	20.4 0.80	1.4 0.06	17.5 0.69	2 0.08	28.1 1.11	6 0.24	5.1 0.20
22 0.87	21.8 0.86	1.6 0.06	18.5 0.73	2 0.08	31.1 1.22	7 0.28	5.1 0.20
23 0.91	22.8 0.90	1.6 0.06	19.5 0.77	2 0.08	31.7 1.25	7 0.28	5.1 0.20
24 0.94	23.8 0.94	1.6 0.06	20.5 0.81	2 0.08	32.2 1.27	7 0.28	5.1 0.20
26 1.02	25.6 1.01	1.6 0.06	22.3 0.88	2.1 0.08	33.2 1.31	7 0.28	5.4 0.21

Specification

- Stainless steel AISI 301
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

Information

GN 111.6 lanyard rings can be rotatably attached to shaft ends or knob hubs using a recess. That way, star knobs can be secured against loss using an additional retaining cable, for example.

All standard parts that can be delivered with loss protection, i.e. with a recess and a lanyard ring, are listed under the service standard GN 111.7 → page 2046.

Ball chains and retaining cables are to be ordered separately.

As a standard, GN 6336.13 star knobs with loss protection → page 584 are already provided with a recess, a mounted lanyard and a retaining cable or a ball chain.

How to order GN 111.6-12-S	1 Diameter d ₀
	2 Type