

# Mounting Clamps

Overview of Types








With mounting clamps, tubes and rods can be fixed with high clamping forces with minimum space requirement. Standardized hole spacings and thread dimensions make the replacement of mounting clamps as well as the handling during installation very simple and efficient, thanks to standardized tools.

The wide range of mounting clamps enables almost any positioning option. The swivel mounting clamps in particular can be combined to a variety of mounting clamp joints.

The aluminum alloy used for the mounting clamps shows high strength and good chemical resistance; the use in contact with food is permitted. The version with black anodized surface is additionally protected against corrosion and is suitable for applications where reflecting surfaces are not desired. Together with the mounting and clamping screws made of corrosion resistant A2 stainless steel, use under unfavorable ambient conditions is possible.













Accessories such as sensor plates, rods and tubes as well as adjustable lever kits and clamping kits complete the range. If required, a suitable retaining magnet (GN 51.6 → [www.jwwinco.com](http://www.jwwinco.com)) is available to facilitate rapid repositioning.

The positioning of sensors, scanners, reflectors, cameras, coolant pipes and air nozzles is a typical practical application.

<p><b>Base Plate Mounting Clamps GN 473</b> Page 1819</p>		<p><b>Mounting Clamps GN 477</b> Page 1820</p>	
<p><b>Two-Way Mounting Clamps GN 474</b> Page 1821</p>		<p><b>Twistable Two-Way Mounting Clamps GN 475</b> Page 1824</p>	
<p><b>T-Mounting Clamps GN 476</b> Page 1826</p>		<p><b>Parallel Mounting Clamps GN 474.1</b> Page 1822</p>	
<p><b>Attachment Mounting Clamps GN 478</b> Page 1827</p>			

# Mounting Clamps

Overview of Types

<p><b>Base Plate Swivel Mounting Clamps</b> GN 485 <a href="http://www.jwwinco.com">www.jwwinco.com</a></p>		<p><b>Swivel Mounting Clamps</b> GN 482 <a href="http://www.jwwinco.com">www.jwwinco.com</a></p>	
<p><b>T-Swivel Mounting Clamps</b> GN 483 <a href="http://www.jwwinco.com">www.jwwinco.com</a></p>		<p><b>Attachment Swivel Mounting Clamps</b> GN 484 <a href="http://www.jwwinco.com">www.jwwinco.com</a></p>	
<p><b>Flanged Mounting Bolts</b> GN 480 Page 1828</p>		<p><b>Rods Tubes</b> GN 480.1 Page 1838</p>	
<p><b>Adjusting Rods, Angled</b> GN 480.3 <a href="http://www.jwwinco.com">www.jwwinco.com</a></p>		<p><b>Adjusting Rods, Cranked</b> GN 480.5 <a href="http://www.jwwinco.com">www.jwwinco.com</a></p>	
<p><b>Hose Adapters</b> GN 480.7 <a href="http://www.jwwinco.com">www.jwwinco.com</a></p>		<p><b>Thread Adapters</b> GN 480.8 <a href="http://www.jwwinco.com">www.jwwinco.com</a></p>	
<p><b>Sensor Brackets</b> GN 479 Page 1830</p>		<p><b>Mounting Brackets</b> GN 479.1 Page 1831</p>	

3.1

3.2

3.3

3.4

3.5

3.6

3.7

3.8

3.9

3.10

